

Hedland



7223N3EF7



SIOPOP®
FR AST

Flame retardant, anti-static hi-vis rain jacket

Flame retardant, anti-static and waterproof, are the main assets of the Hedland. This rain parka has been stylishly designed in a two colour pattern and is equipped with flame retardant reflective tape. It is a very functional parka with two pockets, one chest pocket, one Napoleon pocket, one inside pocket and two loops for gas detection meters. In addition, the separately available hood can be attached to the standing collar or stored in the special inner pocket. The Hedland has sleeves that can be narrowed, and a cord in the hem. Thanks to the I.L.S. system, various fleeces, liners and softshells can be zipped in.



Flame retardant, anti-static hi-vis rain jacket

Hedland - 7223N3EF7

European Standards: (based upon size L)

- » EN ISO 14116 : 2015 / Outer : IND. 1 - Inner : IND.3
- » EN 1149-5 : 2018
- » EN 13034 : 2005 + A1 : 2009 Type PB [6]
- » EN ISO 20471 : 2013 +A1 2016 / Class 3
- » EN 343 : 2019 / Class 3-3-X
- » EN ISO 13688 : 2013

Exterior:

- » Straight collar
- » Provided for hood (hood available separately)
- » YKK zip closure under flap with touch and close fastening
- » 1 patched chest pocket
- » 2 patched pockets with flap
- » 2 loops for gas detectors
- » 1 Napoleon pocket
- » Round sleeves
- » Sleeve narrowing by touch and close fastening
- » Drawstring in hem
- » Slide-in zipper system for extra ease of use
- » Flame retardant reflective tape (50mm)
- » Back length 85 cm (L)

Interior:

- » Fixed flame retardant cotton lining
- » 1 inside pocket
- » Inside pocket for storage of hood
- » Zipper in back lining for applying logo or personalisation
- » Different linings/fleeces can be zipped in

Fabric:

SIOPOR® Fr Ast: 100% polyester fabric with 100% FR PU coating + AST; ± 250 g/m²

Sizes:

XS - 5XL

Colour:

- » 278 Hi-Vis Yellow/Navy
- » 279 Hi-Vis Orange/Navy
- » 815 Hi-Vis Red/Navy

Combining products:

5729 – 5806 – 6133 – 7224 – 7225

I.L.S.:

1666 – 1874 – 2578 – 496Z – 7690 – 7759 – 7760 – 7761 – 7771 – 7870 – 9387 – 9643 – 9644 – 9896

Packaging:

5 pieces per box

Wash and care instructions:



SIOEN head office

Fabriekstraat 23

B-8850 Ardoonie

Belgium

T: +32 (51) 740 800

F: +32 (51) 740 962

www.sioen-ppc.com



Discover
our products

© 2020 Sioen Apparel - Protection through Innovation, Flexothane®, Siopor® and the SIOEN logo are trademarks of the Sioen Industries Group.

Please note that all information given in this document is intended to be useful and informative and is correct to the best of our knowledge at time of print. No liability can be accepted for inaccuracies or omissions. The right is reserved to amend this information without prior notice. All our technical files, style descriptions, presentations, designs and drawings, give the latest update of the standards and design or style features of each product. However, delivered products may comply with previous standards, design or style features. For that Sioen disclaims any liability whatsoever. Contact our sales for full information if specific requirements are needed.