

1324130

<https://www.phoenixcontact.com/in/products/1324130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Replacement die for CRIMPFOX-TC HC 4, CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations

Your advantages

- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1324130
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	BH313Y
GTIN	4063151613723
Weight per piece (including packing)	48.52 g
Weight per piece (excluding packing)	48.1 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

Technical data

Notes

Note on application	For 0.14 mm ² ... 4.0 mm ² solid crimp contacts from the CK1.6 ED..., CK2.5 ED..., CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	--

Product properties

Product type	Die
Compression	Square crimp

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	1 mm ²
AWG min	26
AWG max	18

Crimping position 2

Max. cross section	1.5 mm ²
AWG max	16

Crimping position 3

Max. cross section	2.5 mm ²
AWG max	14

Crimping position 4

Max. cross section	4 mm ²
AWG max	12

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 4 mm ²
Cross section range AWG	26 ... 12

Dimensions

Width	11 mm
Height	35 mm
Length	32 mm

Material specifications

Color	black (RAL 9005)
Material	Steel

CRIMPFOX-TC HC 4/DIE - Replacement die

1324130

<https://www.phoenixcontact.com/in/products/1324130>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1324130>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

Classifications

ECLASS

ECLASS-11.0	21043852
ECLASS-12.0	21043852
ECLASS-13.0	21043852

ETIM

ETIM 9.0	EC001282
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

CRIMPFOX-TC HC 4/DIE - Replacement die

1324130

<https://www.phoenixcontact.com/in/products/1324130>



Accessories

UNIFOX RT-CK 1.6 - Contact removal tool

1072069

<https://www.phoenixcontact.com/in/products/1072069>

Contact removal tool, for turned and rolled CK- 1.6-... contacts



UNIFOX MT-CK 1.6/2.5 - Assembly tool

1089092

<https://www.phoenixcontact.com/in/products/1089092>

Assembly tool, for CK 1.6... crimp contacts for small conductor cross sections



CRIMPFOX-TC HC 4/DIE - Replacement die

1324130

<https://www.phoenixcontact.com/in/products/1324130>



UNIFOX RT-CK 2.5 - Contact removal tool

1072067

<https://www.phoenixcontact.com/in/products/1072067>



Contact removal tool, for turned CK 2,5... contacts

UNIFOX RT-CK 4.0 - Contact removal tool

1072064

<https://www.phoenixcontact.com/in/products/1072064>



Contact removal tool, for rotated CK-4,0-... contacts

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,37F AU - Crimp contact

1266279

<https://www.phoenixcontact.com/in/products/1266279>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.14 mm² ... 0.34 mm², AWG 24 ... 22

CK1,6-ED-0,37M AU - Crimp contact

1266267

<https://www.phoenixcontact.com/in/products/1266267>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.14 mm² ... 0.34 mm², AWG 24 ... 22

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,37F AG - Crimp contact

1266249

<https://www.phoenixcontact.com/in/products/1266249>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.14 mm² ... 0.34 mm², AWG 24 ... 22

CK1,6-ED-0,37M AG - Crimp contact

1266193

<https://www.phoenixcontact.com/in/products/1266193>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.14 mm² ... 0.34 mm², AWG 26 ... 22

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,50M AU - Crimp contact

1266270

<https://www.phoenixcontact.com/in/products/1266270>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm^2 .. 0.5 mm^2 , AWG 20

CK1,6-ED-0,50M AG - Crimp contact

1266195

<https://www.phoenixcontact.com/in/products/1266195>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm^2 ... 0.5 mm^2 , AWG 20

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,50F AU - Crimp contact

1266282

<https://www.phoenixcontact.com/in/products/1266282>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

CK1,6-ED-0,50F AG - Crimp contact

1266252

<https://www.phoenixcontact.com/in/products/1266252>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,75M AU - Crimp contact

1266272

<https://www.phoenixcontact.com/in/products/1266272>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

CK1,6-ED-0,75M AG - Crimp contact

1266450

<https://www.phoenixcontact.com/in/products/1266450>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-0,75F AU - Crimp contact

1266283

<https://www.phoenixcontact.com/in/products/1266283>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

CK1,6-ED-0,75F AG - Crimp contact

1266259

<https://www.phoenixcontact.com/in/products/1266259>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-1,00M AU - Crimp contact

1266274

<https://www.phoenixcontact.com/in/products/1266274>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

CK1,6-ED-1,00M AG - Crimp contact

1266244

<https://www.phoenixcontact.com/in/products/1266244>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm² .. 1 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-1,00F AU - Crimp contact

1266288

<https://www.phoenixcontact.com/in/products/1266288>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

CK1,6-ED-1,50M AU - Crimp contact

1266276

<https://www.phoenixcontact.com/in/products/1266276>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm² .. 1.5 mm², AWG 16

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-1,50M AG - Crimp contact

1266245

<https://www.phoenixcontact.com/in/products/1266245>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CK1,6-ED-1,50F AU - Crimp contact

1266290

<https://www.phoenixcontact.com/in/products/1266290>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CRIMPFOX-TC HC 4/DIE - Replacement die

1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK1,6-ED-1,50F AG - Crimp contact

1266263

<https://www.phoenixcontact.com/in/products/1266263>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CK2,5-ED-0,50F AU - Crimp contact

1273564

<https://www.phoenixcontact.com/in/products/1273564>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-0,50M AG - Crimp contact

1273667

<https://www.phoenixcontact.com/in/products/1273667>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

CK2,5-ED-0,50M AU - Crimp contact

1273601

<https://www.phoenixcontact.com/in/products/1273601>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm² .. 0.5 mm², AWG 20

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-0,50F AG - Crimp contact

1273612

<https://www.phoenixcontact.com/in/products/1273612>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

CK2,5-ED-0,75F AG - Crimp contact

1273611

<https://www.phoenixcontact.com/in/products/1273611>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-1,00M AU - Crimp contact

1273582

<https://www.phoenixcontact.com/in/products/1273582>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

CK2,5-ED-1,00M AG - Crimp contact

1273665

<https://www.phoenixcontact.com/in/products/1273665>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm² .. 1 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-1,00F AU - Crimp contact

1271379

<https://www.phoenixcontact.com/in/products/1271379>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

CK2,5-ED-1,00F AG - Crimp contact

1273610

<https://www.phoenixcontact.com/in/products/1273610>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-1,50M AU - Crimp contact

1273581

<https://www.phoenixcontact.com/in/products/1273581>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm² .. 1.5 mm², AWG 16

CK2,5-ED-1,50M AG - Crimp contact

1273664

<https://www.phoenixcontact.com/in/products/1273664>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-1,50F AU - Crimp contact

1271375

<https://www.phoenixcontact.com/in/products/1271375>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CK2,5-ED-1,50F AG - Crimp contact

1273609

<https://www.phoenixcontact.com/in/products/1273609>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-2,50M AU - Crimp contact

1273572

<https://www.phoenixcontact.com/in/products/1273572>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 2.5 mm² .. 2.5 mm², AWG 14

CK2,5-ED-2,50M AG - Crimp contact

1273663

<https://www.phoenixcontact.com/in/products/1273663>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-2,50F AU - Crimp contact

1271376

<https://www.phoenixcontact.com/in/products/1271376>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

CK2,5-ED-2,50F AG - Crimp contact

1273607

<https://www.phoenixcontact.com/in/products/1273607>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-4,00M AG - Crimp contact

1273620

<https://www.phoenixcontact.com/in/products/1273620>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm² .. 4 mm², AWG 12

CK2,5-ED-4,00M AU - Crimp contact

1273568

<https://www.phoenixcontact.com/in/products/1273568>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 4 mm² ... 4 mm², AWG 12

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK2,5-ED-4,00F AU - Crimp contact

1271372

<https://www.phoenixcontact.com/in/products/1271372>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 4 mm² ... 4 mm², AWG 12

CK2,5-ED-4,00F AG - Crimp contact

1273604

<https://www.phoenixcontact.com/in/products/1273604>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm² ... 4 mm², AWG 12

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK4,0-ED-1,50M AG - Crimp contact

1274097

<https://www.phoenixcontact.com/in/products/1274097>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CK4,0-ED-1,50F AG - Crimp contact

1274089

<https://www.phoenixcontact.com/in/products/1274089>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK4,0-ED-2,50M AG - Crimp contact

1274094

<https://www.phoenixcontact.com/in/products/1274094>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

CK4,0-ED-2,50F AG - Crimp contact

1274088

<https://www.phoenixcontact.com/in/products/1274088>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/in/products/1324130>

CK4,0-ED-4,00M AG - Crimp contact

1274093

<https://www.phoenixcontact.com/in/products/1274093>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm² .. 4 mm², AWG 12

CK4,0-ED-4,00F AG - Crimp contact

1274087

<https://www.phoenixcontact.com/in/products/1274087>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm² .. 4 mm², AWG 12

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in