

LA 10-M10 - Cable connection nut



2112077

<https://www.phoenixcontact.com/in/products/2112077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable connection nut for screwing on threaded bolts, for M10 thread



Commercial data

Item number	2112077
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BE7
Product key	BE733Z
GTIN	4017918052751
Weight per piece (including packing)	26.73 g
Weight per piece (excluding packing)	26.73 g
Customs tariff number	85369010
Country of origin	DE

LA 10-M10 - Cable connection nut



2112077

<https://www.phoenixcontact.com/in/products/2112077>

Technical data

Product properties

Product type	Mounting material
Type	Cable connection nut

Connection data

Screw thread	M10
Stripping length	8 mm
Conductor cross section rigid	0.5 mm ² ... 16 mm ²
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross section flexible	0.5 mm ² ... 10 mm ²
Conductor cross section, flexible [AWG]	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 10 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²

Dimensions

Width	17 mm
Height	37.1 mm
Depth	37.1 mm

Material specifications

Material	PA 6.6
Flammability rating according to UL 94	V2

LA 10-M10 - Cable connection nut



2112077

<https://www.phoenixcontact.com/in/products/2112077>

Classifications

ECLASS

ECLASS-11.0	27182807
ECLASS-12.0	27182807
ECLASS-13.0	27182807

ETIM

ETIM 9.0	EC002625
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

LA 10-M10 - Cable connection nut



2112077

<https://www.phoenixcontact.com/in/products/2112077>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in