

PC connectable Desktop Labelling machine



There's no messing around with the PT-9700PC. This high speed, high quality professional label printer gives you wide, durable labels in an instant. Perfect for where many labels are required quickly, such as manufacturing, event management, filing systems and asset management.

Key Features

- Save time with up to 80mm per second
- 3.5, 6, 9, 12, 18, 24 & 36mm wide durable labels available
- Convenient built-in automatic cutter
- Space saving compact, stylish design
- Includes 36mm black on white HG tape (8m) and AC Adapter.

Supplies

3.5 mm	6 mm	9 mm	12 mm	18 mm	24 mm	36 mm
Standard Laminated - 8m						
TZe-111	TZe-121	TZe-131	TZe-141	TZe-151	TZe-161	
		TZe-132				
		TZe-133				
		TZe-134		TZe-145		
TZe-211	TZe-221	TZe-231	TZe-241	TZe-251	TZe-261	
		TZe-231S*				
	TZe-222	TZe-232	TZe-242	TZe-252	TZe-262	
	TZe-223	TZe-233	TZe-243	TZe-253	TZe-263	
		TZe-334	TZe-344	TZe-354		
TZe-315	TZe-325	TZe-335	TZe-345	TZe-355	TZe-365	
	TZe-421	TZe-431	TZe-441	TZe-451	TZe-461	
		TZe-431S*				
		TZe-435				
	TZe-521	TZe-531	TZe-541	TZe-551	TZe-561	
		TZe-535		TZe-555		
TZe-611	TZe-621	TZe-631	TZe-641	TZe-651	TZe-661	
	TZe-721	TZe-731	TZe-741	TZe-751		
Fluorescent Laminated - 5m						
		TZe-931		TZe-B61		
		TZe-C31		TZe-C51		
Matt Laminated - 8m						
		TZe-M31				
		TZe-MQ35**				
		TZe-MQP35**				
		TZe-MQG35**				
Metallic Laminated - 8m						
		TZe-M931		TZe-M951	TZe-M961	
Non-Laminated - 8m						
TZe-N201	TZe-N221	TZe-N231	TZe-N241	TZe-N251		
Flexible-ID Laminated - 8m						
TZe-FX211	TZe-FX221	TZe-FX231	TZe-FX241	TZe-FX251	TZe-FX261	
TZe-FX611	TZe-FX621	TZe-FX631	TZe-FX641	TZe-FX651	TZe-FX661	
Strong Adhesive Laminated - 8m						
TZe-S121	TZe-S131	TZe-S141	TZe-S151			
TZe-S221	TZe-S231	TZe-S241	TZe-S251	TZe-S261		
	TZe-S621	TZe-S631	TZe-S641	TZe-S651		
Fabric - 3m						
		TZe-F43	TZe-F44B			
Security Laminated - 8m						
				TZe-SE4		

Optional Extras

- AD24ES AC adapter

Product Specifications

Housing Colour	Light Grey & Pearl White
Key Board	N/A
Number of Keys	2 (Power On/Off, feed & cut)
Cutter	Yes (Auto (full/half))
Power	AC adapter (included)
Interface	USB 2.0 (Full Speed)
LCD	LED Lamp
Print Method	Thermal
Print Head	360dpi/ 384dots
Print Speed	80 mm / sec (HG Tape) 20mm / sec (Tze Tape)
Tape Type	HG & TZe
Tape Width	Max. Label width 36mm
Max. Print Width	27.1mm
Number of characters	N/A
Number of Symbols	N/A
Character Sizes	PT-Editor 5 software
Fonts	Windows Fonts
Font Styles	PT-Editor 5 software
Frames	PT-Editor 5 software
Underline	PT-Editor 5 software
Strikeout	PT-Editor 5 software
Multi-Line	PT-Editor 5 software
Horizontal Alignment	PT-Editor 5 software
Vertical Alignment	PT-Editor 5 software
Tape Length Setting	PT-Editor 5 software
Tape Margin Setting	PT-Editor 5 software
Pre made Designs	N/A
Memory	N/A
Barcodes	PT-Editor 5 software
Time and Date function	No
Numbering	PT-Editor 5 software
Mirror Printing	PT-Editor 5 software
Vertical Printing	PT-Editor 5 software
Repeat printing	PT-Editor 5 software
Print Preview	PT-Editor 5 software
Unit	N/A
Language Change	N/A

Weights/ Dimensions/ Measures

Dimensions

116mm x 192.7mm x 140mm

Weight

1.57kg

What's in the box

36mm Black on White HG laminated tape (8M)

AC Adapter

USB cable

Users Guide

Warranty Card

