




Part Number : [50579310](#)
Product Description : SL Crimp Housing,
Single Row, Version D, Back Ribs, 10 Circuits,
Black
Series Number : 70066
Status : Active
Product Category : Connector Housings
Engineering Number : 70066-0114



Documents & Resources

Drawings

[050579310_sd.pdf](#)
[PK-70066-100-001.pdf](#)

3D Models and Design Files


[050579310_stp.zip](#)

Specifications

[PS-70058-001.pdf](#)
[PS-70400-001.pdf](#)
[PS-71851-001.pdf](#)
[TS-70058-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	70066
Description	SL Crimp Housing, Single Row, Version D, Back Ribs, 10 Circuits, Black
Application	Signal, Wire-to-Board
Comments	Version D
Product Name	SL
UPC	800753724853

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	None

Material - Resin	Polyester Alloy
Net Weight	0.072/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.54mm SL Interim Clips	<u>70013</u>
SL Dual Row Housing Panel Mounts	<u>70022</u>
SL Single Row, Version D, Male FFC/FPC Connectors	<u>70431</u>
SL Single Row Male Insulation Displacement Connector Assemblies	<u>70475</u>
SL Vertical Single Row Headers	<u>70543</u>
SL Right-Angle, Single Row, Low Profile Headers	<u>70553</u>

Use with Part(s)

Description	Part Number
SL Male Terminals	<u>70021</u>
SL Female Terminals	<u>70058</u>
SL Female Terminals	<u>71851</u>