

Datasheet

MAX ROUTING TRUNKING

A cost effective system designed to meet the expectations of a demanding cable management market. Suitable for a wide range of installations, including warehouses, trading premises and other industrial sites.

- MAX range provides a sturdy, neat solution
- Base profile is pre-punched for ease of installation
- Comprehensive range of accessories including moulded and fabricated
- A unique cable retainer system allows the clips to act as a cable support shelf during installation

**Standard supply:**

Base and cover packed together

Material:

PVC-U 1309

Supplied length:

3 mtr

Size:

50x50mm



Colour:








RAL 9010 Pure White

75x75mm

100x100mm


Bespoke fabrications can be made upon request, please contact your regional sales office.




		MAX	MAX
	Height/Width	50x50	75x75
Base & Cover	RAL 9010 Pure White Art.No.	843-1572	843-1581
	Pack/mtr	24	24
			
Internal Corner (moulded)	RAL 9010 Pure White Art.No.	843-1588*	843-1607**
	Dimension "a,b" mm	75,24	100,24
	Pack/pc	5	5
			
External Corner (moulded)	RAL 9010 Pure White Art.No.	843-1597*	843-1601**
	Dimension "a,b" mm	75,24	100,24
	Pack/pc	5	5
			
Flat Angle	RAL 9010 Pure White Art.No.	843-1590	843-1610
	Dimension "a,b" mm	200,147	200,147
	Pack/pc	1	1
			
Flat Tee	RAL 9010 Pure White Art.No.	843-1594	843-1613
	Dimension "a,b,c,d" mm	270,210,90,60	270,210,90,60
	Pack/pc	1	1
			
Cable Shelf - 50mm	RAL 9010 Pure White Art.No.	-	-
	Pack/pc	-	-
			
End Cap	RAL 9010 Pure White Art.No.	843-1604	843-1617
	Pack/pc	5	5
			

* Use of standard mouldings is only possible with columns equal to or greater than 120mm deep x 70mm wide.


** Use of standard mouldings is only possible with columns equal to or greater than 145mm deep x 70mm wide.




		MAX
	Height/Width	100x100
Base & Cover	RAL 9010 Pure White Art.No.	843-1584
	Pack/mtr	12




Internal Corner	RAL 9010 Pure White Art.No.	843-1626
	Dimension "a,b" mm	110,147
	Pack/pc	1





External Corner	RAL 9010 Pure White Art.No.	843-1629
	Dimension "a,b" mm	200,147
	Pack/pc	1



Flat Angle	RAL 9010 Pure White Art.No.	843-1623
	Dimension "a,b" mm	200,147
	Pack/pc	1



		MAX	
	Height/Width	100x100	
Flat Tee	RAL 9010 Pure White Art.No.	843-1632	
	Dimension "a,b,c,d" mm	355,255,110,60	
	Pack/pc	1	
End Cap	RAL 9010 Pure White Art.No.	843-1635	
	Pack/pc	5	