

Cable ends, Linergy TR cable ends, single conductor, red, 1mm², for insulated cable, long size, 10 sets of 100

DZ5CE010L12D

① Discontinued

Main

Range of Product	Linergy	
Product or Component Type	Cable end	
Cable end size	Long	
Standards	DIN 46228-4	
Type of Packing	String of bags	
Quantity per Set	10 sets of 100	
Cable cross section	0.002 in² (1 mm²)	

Complementary

Cable end type	Single conductor	
Additional information	Without marker tag holder	
Color	Red	
Bezel material	Halogen-free plastic	
Tube material	Copper ISO 1337	
Number of cables	1	
AWG Gauge	AWG 18	
Bezel size	Ø 3.5 mm	
Tube diameter	0.07 in (1.7 mm)	
Length	0.7 in (18 mm)	
Tube length	0.5 in (12 mm)	
Product Weight	0.33 lb(US) (0.15 kg)	

Environment

Ambient air temperature for -4...221 °F (-20...105 °C) operation

Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES	
Discount Schedule	ı	
GTIN	3389110211344	
Returnability	No	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	0.16 in (0.400 cm)	
Package 1 Width	0.16 in (0.400 cm)	
Package 1 Length	0.55 in (1.400 cm)	
Package 1 Weight	0.004 oz (0.100 g)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	1000	
Package 2 Height	1.18 in (3.000 cm)	
Package 2 Width	4.33 in (11.000 cm)	
Package 2 Length	8.27 in (21.000 cm)	
Package 2 Weight	4.832 oz (137.000 g)	
Unit Type of Package 3	S01	
Number of Units in Package 3	15000	
Package 3 Height	5.91 in (15.000 cm)	
Package 3 Width	5.91 in (15.000 cm)	
Package 3 Length	15.75 in (40.000 cm)	
Package 3 Weight	4.989 lb(US) (2.263 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free plastic parts product
Take-back	No