



## PX140

Comfort and protection for lightweight applications



Multi Purpose



Light Duty

## Comfortable safety gloves granting superb dexterity for lightweight applications

- **Advanced defenses:** PX140 work gloves are made from tough polyurethane coating that provides exceptional personal protection against abrasion and deterioration
- **Enhanced features:** Designed for a comfortable fit, these abrasion-resistant, industrial gloves feature an elasticated knit wrist that ensures they are secure around the wrist
- **Elevated comfort:** These protective gloves are designed with a ventilated back design that ensures the hand can breathe naturally even during prolonged periods of wear



- Automotive
- Chassis assembly, body trimming



## PX140

Comfort and protection for lightweight applications

- **Polyurethane coating:** Strong resistance to wear and tear
- **Elasticated knitwrist:** Ensures a snug fit
- **Ventilated back design:** Improved breathability



EN388: 2016



3131A

PX140	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Nylon <b>Cuff Style:</b> Knitwrist	15	6, 7, 8, 9, 10	220-260 mm/8.6-10.2 inches	White	1 pair/pack, 12 pairs/bag, 20 bags/carton
-------	--	----	----------------	----------------------------	-------	---

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

