

TECHNICAL DATA

MOISTURE GUARD SPRAY (CLEAR)

Indoor corrosion preventative

Description

ROCOL Moisture Guard Spray (Clear) is a thin, almost dry corrosion preventative film suitable for the temporary indoor protection of components such as bearings, gears, pressings and any machined metal product which requires protection from corrosive attack - whether in storage, transit or between operations.

ROCOL Moisture Guard Spray (Clear) is ideal as a colourless, medium/long term indoor corrosion protection of bare metal components and mould tools particularly where condensation is a problem.

Outstanding Features

- **Effective indoor corrosion protection**
- **Tenacious soft film - easily handled**
- **Almost dry film - does not attract dirt and dust**
- **Particularly effective in damp or humid environments**

Directions for use

Shake well, hold upright and spray from a distance of approximately 15-30cm (6-12 inches). One pass usually provides sufficient protection. Ensure adequate ventilation. Do not spray onto naked flame or any incandescent material.

N.B. Test compatibility with painted or coated surfaces, plastics and rubbers if the product is liable to come into contact with these materials.

Technical Data

<i>Propellant</i>	: <i>Hydrocarbon blend</i>
<i>Solvent</i>	: <i>Non-chlorinated hydrocarbon</i>
<i>Colour</i>	: <i>Clear</i>
<i>Film type</i>	: <i>Almost dry, soft flexible film</i>
<i>Film thickness (Typical)</i>	: <i>Approximately 3 to 5 microns</i>
<i>Curing time</i>	: <i>Touch dry within 15 to 30 minutes</i>
<i>Protection period</i>	: <i>6-12 months indoors, Short term outdoors</i>

ROCOL Limited

ROCOL House, Swillington, Leeds LS26 8BS, England.

Tel: 0113 232 2600 Fax: 0113 232 2760

ROCOL is a BS EN ISO 9002 registered company.

ROCOL is a trade mark of ROCOL Limited

The information in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which effect the use and performance of our products for which reason the information in this publication is given without responsibility

Moisture Guard Spray (Clear)

Technical Data cont'd:

Storage : *Storage temperature should be kept below 50°C. Storage area should be out of direct sunlight.*

Health and Safety

Further Technical Data and Health and Safety information (COSHH, MSDS) is available from the Customer Service Department, ROCOL Ltd., ROCOL House, Swillington, Leeds, LS26 8BS, England.

Telephone: 0113 232 2700, (When calling from outside UK: 44 113 232 2700).

Fax: 0113 232 2760, (When faxing from outside UK: 44 113 232 2760).

Issue: 6902a 10/07/96

ROCOL Limited

ROCOL House, Swillington, Leeds LS26 8BS, England.

Tel: 0113 232 2600 Fax: 0113 232 2760

ROCOL is a BS EN ISO 9002 registered company.

ROCOL is a trade mark of ROCOL Limited

The information in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which effect the use and performance of our products for which reason the information in this publication is given without responsibility