


A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/gb/products/1415224>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pressure compensation element, material for screw connection: Stainless steel 1.4305, connecting thread: M12 x 1.5, color: silver-colored, with O-ring

Your advantages

- Reduces the formation of condensation

Commercial data

Item number	1415224
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 695 (C-2-2019)
GTIN	4055626038674
Weight per piece (including packing)	15.81 g
Weight per piece (excluding packing)	15.81 g
Customs tariff number	73269098
Country of origin	RO

A-INB-M12-69KN-S-S - Pressure compensation element



1415224

<https://www.phoenixcontact.com/gb/products/1415224>

Technical data


Product properties

Product type	Pressure compensation element
Air flow rate	16 l/h (at Δ min. 70 mbar)

Connection data

Tightening torque	0.5 Nm ... 1 Nm (Flange)
-------------------	--------------------------

Dimensions

Dimensional drawing	
Length	21 mm
Length of the connecting thread	10 mm
Length without connecting thread	11 mm
Diameter	12 mm
Connecting thread diameter	12 mm
Wrench size, union nut	17 mm
Hexagon angular dimension	18.5 mm
Thread type connection side	M12 x 1.5
Thread pitch	1.5 mm

Material specifications

Color	Steel/stainless steel color
Material	Acrylic copolymer (Venting filter) Stainless steel 1.4305 (Housing)
Seal material	Perbunan
Material for screw connection	Stainless steel 1.4305

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 IP67 IP69
Ambient temperature (operation)	-40 °C ... 105 °C


A-INB-M12-69KN-S-S - Pressure compensation element

1415224

<https://www.phoenixcontact.com/gb/products/1415224>

Drawings

Dimensional drawing



A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/gb/products/1415224>

Classifications

ECLASS

ECLASS-13.0	27440192
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/gb/products/1415224>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk