

Previously known as: Universal 87-665

Light-duty natural latex rubber gloves, combining tactile sensitivity and tensile strength

- **Enhanced sensitivity and strength:** Made from 100% natural latex rubber, AlphaTec® 87-665 durable work gloves are the standard choice in their segment, combining tactile sensitivity with excellent tensile strength
- **Elevated comfort:** As these hand protection gloves feature 100% cotton flocking, they grant wearers a softer feel and absorb perspiration
- **Assured cleanliness:** These blue protective gloves are specially treated with chlorine, maximizing cleanliness and minimizing allergic reaction risks

Industries

- Automotive
- Chemical
- Oil and gas
- Maintenance
- Janitorial / Sanitation

Applications

- Chemical processing and preparation
- Janitorial use
- Light assembly tasks
- Maintenance of plant and machines



Previously known as: Universal 87-665

Key Features

- **100% natural latex rubber:** A balance of sensitivity and tensile strength
- **Pure cotton flocking:** Sweat and moisture absorption, for increased comfort
- **Chlorination treatment:** Improved cleanliness, fewer allergy risks

Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493

EN388: 2016



1010A

EN ISO 374-1:2016



KLP

EN ISO 374-5



VIRUS

EN 421



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec®87-665	Liner Material: N/A Coating Material: Natural Rubber Latex	6.5 - 7, 7.5 - 8, 8.5 - 9, 9.5 - 10	305 / 12	Blue	• 12 pairs per bag, 12 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.