



**Part Number :** [08580187](#)

**Product Description :** KK Trifurcon Crimp Terminal  
6438, 20-18 AWG, Reel, Phosphor Bronze Gold (Au)

**Series Number :** 6838

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Number :** 6838-A(P558)

**Packaging Alternative :** [08580189](#) (Bag)



---

## Documents & Resources

### Drawings

[008580187\\_sd.pdf](#)

[PK-2759-002-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-40-02-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	6838
Description	KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Gold (Au)
Application	Power, Wire-to-Board
Product Name	KK 396,Trifurcon
UPC	800753614253

### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.198/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size (AWG)	18, 20
Wire Size mm <sup>2</sup>	N/A

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Use with Part(s)

Description	Part Number
KK 3.96mm Crimp Housings	<u>41695</u>
KK 3.96mm Pitch Single Row Crimp Housings	<u>6442</u>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<u>11030016</u>
Terminator Die	<u>11402096</u>
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG	<u>638279500</u>
Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals, 24-18 AWG, check ATS for Wire Insulation Diameter Compatibility	<u>638885000</u>