


XTL™ Labels



Pre-Sized Labels

- Ideal for flat surface labelling like barcodes, faceplates, shelves, bins, beams and more
- Constructed of a glossy polyester material and coated with industrial-grade adhesive
- Facilitate batch label printing to improve productivity
- Pre-Sized labels make applying labels quick and easy
- Durable thermal transfer printing technology – label text won't smear or fade
- RoHS compliant



Quick Specs	
Label Widths	9 mm, 12 mm, 19 mm, 25 mm, 51 mm
Tape Platform	XTL
Printer Compatibility	XTL 300: Up to 19 mm width XTL 500: Up to 51 mm width
Printing System	Thermal Transfer
Temperature Rating	-40°C to 60°C
UL Recognized	Component to UL 969
Country of Origin	Belgium
Material	Polyester

Item Number	Width (mm)	Length (mm)	Colour	Quantity of Pre-Sized Labels		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	UPC
1868665	12	12	A	250	Unit	72	35	120	0.08	1	071701000576
					Shelf	215	76	126	0.52	6	30071701000577
					Case	400	230	145	2.88	30	50071701000571
					Pallet	1200	800	1165	206.44	63	-
1868666	12	25	A	250	Unit	72	35	120	0.08	1	071701000583
					Shelf	215	76	126	0.52	6	30071701000584
					Case	400	230	145	2.88	30	50071701000588
					Pallet	1200	800	1165	206.44	63	-

DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand
 ©2015 Newell Europe LLC

XTL™ Labels



Item Number	Width	Length	Colour	Quantity of Pre-Sized Labels		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	UPC
1868667	12	38	A	185	Unit	72	35	120	0.08	1	071701000590
					Shelf	215	76	126	0.52	6	30071701000591
					Case	400	230	145	2.88	30	50071701000595
					Pallet	1200	800	1165	206.44	63	-
1868668	25	25	A	250	Unit	72	65	120	0.14	1	071701000606
					Shelf	215	76	126	0.46	3	30071701000607
					Case	400	230	145	2.61	15	50071701000601
					Pallet	1200	800	1165	189.43	63	-
1868669	9	25	A	250	Unit	72	35	120	0.08	1	071701000613
					Shelf	215	76	126	0.52	6	30071701000614
					Case	400	230	145	2.89	30	50071701000618
					Pallet	1200	800	1165	207.38	63	-
1868670	12	19	A	250	Unit	72	35	120	0.08	1	071701000620
					Shelf	215	76	126	0.52	6	30071701000621
					Case	400	230	145	2.89	30	50071701000625
					Pallet	1200	800	1165	207.38	63	-
1868701	19	25	A	250	Unit	72	35	120	0.09	1	071701000637
					Shelf	215	76	126	0.59	6	30071701000638
					Case	400	230	145	3.25	30	50071701000632
					Pallet	1200	800	1165	230.06	63	-
1868702	25	51	A	100	Unit	72	65	120	0.14	1	071701000644
					Shelf	215	76	126	0.46	3	30071701000645
					Case	400	230	145	2.61	15	50071701000649
					Pallet	1200	800	1165	189.43	63	-
1868703	51	76	A	100	Unit	72	65	120	0.17	1	071701000651
					Shelf	215	76	126	0.56	3	30071701000652
					Case	400	230	145	3.12	15	50071701000656
					Pallet	1200	800	1165	221.56	63	-

DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand

©2015 Newell Europe LLC