

Powerful single motor upright vacuum cleaner

**Equipment:**

- Crevice tool
- Upholstery tool
- Detachable suction tube
- Corrugated suction hose
- Filter bag Fleece
- Filter status indicator
- Height-adjustable handle
- Safety class II
- Roller brush 1 piece(s)

**Order no.: 1.023-111.0**

**Technical data**

Working width (mm)	300
Air flow rate (l/s)	48
Vacuum (mbar/kPa)	207/20.7
Container capacity (l)	5.5
Max. intake performance (W)	max. 1150
Standard nominal size (mm)	35
Length of cord access. (m)	12
Sound level (db(A))	67
Sound power level (db(A))	80
Quantity of motors	-
Power rating brush (W)	-
Weight (kg)	8.4
Dimensions (L x W x H) (mm)	320x310x1220
Energy efficiency class	D

## Details

### Description

Kärcher's CV 30/1 upright vacuum cleaner uses a single high performance motor to drive both the suction fan and brush, making the machine easy to carry and manoeuvre. This machine combines high suction power with the ability to clean deep into the carpet pile thanks to a height-adjustable brush. Equipped with a detachable suction tube for vacuuming upholstery and hard to reach areas, it is ideal for cleaning carpeted areas quickly and efficiently.

---

### Features & Benefits

Excellent cleaning

The corrugated suction hose is easy to remove. This enables blockages to be cleared quickly and effortlessly.

Patented centrifugal coupling

For a longer service life: the innovative, patented centrifugal coupling protects the entire brush head against overload thus avoiding high service costs.

---

## Accessories

### Crevice nozzles

#### Crevice tool ID 35.

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 250 mm.

Order no. 6.906-240.0



### Fabric filter bag

#### Fabric filter bag

Cotton, washable (40°C)

Order no. 6.904-301.0



### Fleece filter bags (3 ply)

#### Fleece filter bags CV 30/1, CV 38/1, x10

3-ply tear-resistant fleece filter bags, dust class M, standard for CV 30/1 and CV 38/1. Contents: x10.

Order no. 6.904-305.0



### HEPA filter for dust class H

#### HEPA exhaust air filter cassette

HEPA filter cassette, glass fibre in plastic frame, Dust class H 12

Order no. 6.414-760.0



### Paper filter (2 ply)

#### Paper filter bags

Paper filter bags, dust class M suitable for all CV 30/1 and CV 38/1 models. Contents: x10.

Order no. 6.904-294.0



#### Paper filter bags, bulk consumer pack

Dust class M / large-scale consumer pack

Order no. 6.904-303.0



### Reducer (tube -> nozzle)

#### Reducer from ID 35 to 32

Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.

Order no. 6.902-072.0



### Roller brushes for upright vacuum cleaners

#### Roller brush

Black (normal), soft bristles.

Order no. 6.906-641.0



#### Roller brush

Red, hard bristles (e.g. for needled felt)

Order no. 6.906-642.0



## Suction brushes

### Suction brush

Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.



**Order no. 6.903-862.0**

---