



Brand of NTN corporation

Technical data



2306EEG15

Double-row self-aligning ball bearings



Self-aligning ball bearing, polyamide cage, friction seals on both sides

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	30 mm
D - External diameter	72 mm
B - Bearing/Inner ring width	27 mm
d1 - External diameter inner ring	40,5 mm
D1 - Inner diameter outer ring	62,8 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,54 kg

PRODUCT PERFORMANCE

C - Dynamic load	21300000 mN
C0 - Static load	6300000 mN
Cu - Fatigue limit load	290000 mN
e - Coefficient	0.26
Y0 - Static axial load coefficient	2.51
Y1 - Lower axial load coefficient	2.4
Y2 - Upper axial load coefficient	3.71
N lim - Mechanical Limit Speed	36600 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	5.312 Hz
---	----------



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

2306EEG15

Double-row self-aligning ball bearings

BEARING FREQUENCIES

BPFI - Over rolling frequency on inner (60 rpm)	7.688 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	5.21 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.605 Hz
FTF - Rotational frequency - cage (60 rpm)	0.409 Hz

ABUTMENT

da min - Min shoulder diameter IR	36,5 mm
Da max - Max shoulder diameter OR	65,5 mm
ra max - Max shaft & housing fillet radius	1 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15