

Features

- **Pre-Equipped with Devices** – Comes fully loaded with mechanical isolation lockout devices for immediate use.
- Shadows indicate missing or in-use devices, improving visual management and accountability.
- Built with 4mm Aluminium Composite Panel for long-lasting industrial use.
- Ideal for placement near machines to support point-of-use lockout in mechanical maintenance zones.
- Efficient Organisation – Keeps tools neatly arranged and easily accessible, minimising search time during critical operations.
- **Mounting Hardware Included** – Ready for installation with all necessary mounting components supplied.

RS PRO Shadow Lockout Station - Mechanical (With Devices)

RS Stock No.: 0694388



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Shadow Lockout Station is a purpose-built, wall-mounted LOTO board designed to centralise mechanical isolation devices near machines.*
- *Pre-equipped with essential LOTO devices, it ensures immediate readiness for energy isolation procedures.*
- *Features a shadow layout, helping personnel identify missing or in-use tools at a glance.*
- *Built from 4 mm ACP sheets with rounded corners, providing strength, longevity, and user safety.*
- *Tailored for mechanical departments and maintenance areas, the board supports efficient, localised LOTO operations.*
- *Mounting hardware is included, enabling fast and secure installation in any industrial environment.*
- *Designed to improve safety compliance, reduce equipment downtime, and promote organized lockout management.*

General Specifications

Type	Shadow Lockout Station
Material	4mm ACP boards
Colour	Blue & White
Package	BOPP + Box

Mechanical Specifications

Dimensions	1181mm x 1194mm
Width	1181mm
Height	1194mm
Weight	14.80 Kgs

Operation Environment Specifications

Withstand temperature	-20°C to +80°C
------------------------------	----------------

Station Components:

Item Name	Item Description	Quantity
Lockout Hasp	Vinyl Coated Hasp – Small (25mm)	2

Lockout Hasp	Vinyl Coated Hasp – Premier (38mm)	2
Lockout Hasp	Stainless Steel Hasp – 25mm shackle	2
Lockout Padlock	Premier Lockout Safety Padlock – Steel Shackle – Key Different (Red)	10
Gate Valve Lockout	Gate Valve Lockout – 02	1
Gate Valve Lockout	Gate Valve Lockout – 04	1
Gate Valve Lockout	Gate Valve Lockout – 06	1
Gate Valve Lockout	Gate Valve Lockout – 08	1
Gate Valve Lockout	Gate Valve Lockout – 10	1
Ball Valve Lockout	Top Rail – Ball Valve Lockout – Small	1
Ball Valve Lockout	Top Rail – Ball Valve Lockout – Large	1
Butterfly Valve Lockout	Butterfly Valve Lockout	1
Multipurpose Cable Lockout	Economy Multipurpose Cable Lockout with 2 Mtrs. Vinyl Coated Steel Cable	1
Multipurpose Cable Lockout	Metallic Multipurpose Cable Lockout with 2 Mtrs. Stainless Steel Cable	1
Cylinder Lockout	Cylinder Lockout (Yellow Lid)	1
Mushroom Lockout	Normal Push Button Lockout for Electrical Panels	1
Pneumatic Lockout	Pneumatic Lockout – Straight with 9 Holes	1
Lockout Sign	Hanging Lockout Sign (8 x 6 inch)	1
Lockout Tags	“Do Not Operate” Lockout Tags	20
Lockout Ties	10” Nylon Ties for Tags	20
Lockout Pen	Black Marker Pen for Tags	1
Shadow Lockout Station	Shadow Station Board - Mechanical Department	1
Butterfly Valve Lockout	Stainless Steel Butterfly Valve with Pull Handle Adjustable Lockout	1
Valve Lockout	Universal Valve Lockout with Small Arm	1