



Chemical protection

ULTRANITRIL 454

Splashes | short wear



CHEMICAL PROTECTION
TYPE B

EN388



2000X

EN ISO 374-1



TYPE B
KPT

EN ISO 374-5



CATEGORY 3

DEXTERITY



0334

EN420:
5/5

Precision dexterity in mildly aggressive environments, for those sensitive to natural latex

SPECIFIC ADVANTAGES



Comfort

- Outstanding precision dexterity, due to the qualities of MAPA's unique synthetic material
- Optimal comfort: anatomical shape, new flocking quality



Productivity

- Good handling of slippery objects, due to the embossed texture



Skin protection

- Latex free to reduce the risk of allergies
- Hypoallergenic



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Optimised individual packaging to limit plastic waste
- Recycled material in the packaging: 30 %

INDUSTRIES

- Local Authorities (Cleaning)
- Health

APPLICATIONS

- Common Tasks in hospitals and clinics
- Handling household detergents



Chemical protection

ULTRANITRIL 454

Splashes | short wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
2 0 0 0 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	K: Sodium hydroxide 40%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
TYPE B	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Embossed texture
Material	Nitrile
Cuff characteristic	Straight cuff
Colour.s	Green Blue
Length (cm)	31
Thickness (mm)	0.35
European sizes	6 7 8 9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/box 50 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/05/18/0908
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France