

FEATURES

- VDE approved
- Rigid PVC, white RAL 9010
- Dimensions available:
 - 15 x 15 mm
 - 18 x 18 mm
 - 30 x 30 mm
 - 40 x 40 mm
 - 60 x 40 mm
 - 60 x 60 mm
 - 90 x 60 mm
 - 110 x 60 mm
- 2 m length
- Base including cover
- Hardly-inflammable, self-extinguishing
- Perforated bottom
- Ideal for new installation or renovation
- Designed for the use of dividers from size 60x60 mm onwards
- Two cable holders included from size 60x40 mm onwards
- External and internal corners and end caps available from size 40x40mm onwards

RS PRO VDE Installation Trunking



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Product details:

- PVC installation trunking in white colour RAL 9010, with cover included
- For direct installation on wall and ceiling
- The material is hardly-inflammable and self-extinguishing
- The base with perforated bottom (distance 125 mm) allows an easy installation with screws
- Ideal for new installation or renovation
- The trunking is designed for the use of dividers from 60 x 60 mm onwards
- Two included cable holders per meter from 60 x 40 mm onwards for easy installation
- External corner parts, internal corner parts and end caps are available from size 40 x 40 mm onwards

General Specifications

Colour	White, RAL 9010
---------------	-----------------

Mechanical Specifications

Material	PVC (Polyvinylchlorid)
-----------------	------------------------

Approvals


Standards	VDE compliant DIN EN 50085-1 and DIN EN 50085-2-1
RoHS compliant	yes

Similar Products


Stock No.	GTIN	Product Name	Width	Height	Length / Piece	Pack Size
237-4039	5059044316818	Installation Trunking	15 mm	15 mm	2 m	14 m
237-4037	5059044316696	Installation Trunking	15 mm	15 mm	2 m	140 m
237-4041	5059044316825	Installation Trunking	18 mm	18 mm	2 m	16 m
237-4040	5059044316702	Installation Trunking	18 mm	18 mm	2 m	96 m
237-4043	5059044316832	Installation Trunking	30 mm	30 mm	2 m	10 m
237-4042	5059044316719	Installation Trunking	30 mm	30 mm	2 m	50 m
237-4046	5059044316856	Installation Trunking	40 mm	40 mm	2 m	32 m
237-4047	5059044316733	Installation Trunking	40 mm	40 mm	2 m	8 m
237-4049	5059044316863	Installation Trunking	60 mm	40 mm	2 m	14 m
237-4048	5059044316740	Installation Trunking	60 mm	40 mm	2 m	28 m
237-4052	5059044316870	Installation Trunking	60 mm	60 mm	2 m	8 m
237-4051	5059044316757	Installation Trunking	60 mm	60 mm	2 m	24 m
237-4054	5059044316887	Installation Trunking	80 mm	60 mm	2 m	6 m
237-4053	5059044316764	Installation Trunking	80 mm	60 mm	2 m	24 m
237-4056	5059044316894	Installation Trunking	110 mm	60 mm	2 m	4 m
237-4055	5059044316771	Installation Trunking	110 mm	60 mm	2 m	16 m
Accessories						
237-4045	5059044316849	5 x 2 m Divider	for use with trunking from 60 mm			10 m
237-4044	5059044316726	40 x 2 m Divider	for use with trunking from 60 mm			80 m
221-5310	5059044259597	External Corner	for 40 x 40 mm trunking			1 piece
221-5312	5059044259603	Internal Corner	for 40 x 40 mm trunking			1 piece
221-5313	5059044259610	End Cap	for 40 x 40 mm trunking			1 piece
221-5314	5059044259627	External Corner	for 60 x 40 mm trunking			1 piece
221-5315	5059044259634	Internal Corner	for 60 x 40 mm trunking			1 piece
221-5316	5059044259641	End Cap	for 60 x 40 mm trunking			1 piece
221-5317	5059044259658	External Corner	for 60 x 60 mm trunking			1 piece
221-5318	5059044259665	Internal Corner	for 60 x 60 mm trunking			1 piece
221-5319	5059044259672	End Cap	for 60 x 60 mm trunking			1 piece
221-5320	5059044259689	External Corner	for 90 x 60 mm trunking			1 piece
221-5321	5059044259696	Internal Corner	for 90 x 60 mm trunking			1 piece
221-5322	5059044259702	End Cap	for 90 x 60 mm trunking			1 piece
221-5323	5059044259719	External Corner	for 110 x 60 mm trunking			1 piece
221-5324	5059044259726	Internal Corner	for 110 x 60 mm trunking			1 piece
221-5319	5059044259672	End Cap	for 110 x 60 mm trunking			1 piece

Accessories

External Corner



Internal Corner



End Cap



Divider

