

BW 2400S XL9/E-XXL


Mobile roller cab with 9 drawers, with anti-tilt system, long model, with assortment of 716 tools

- 9 drawers (882x367 mm), with ball bearing slides: 8 drawers, 70 mm high 1 drawer, 140 mm high.
- Sturdy ABS worktop, with 6 tote-trays
- Study nylon front, with built-in label holder
- Drawer bases protected by foamed rubber mats
- Four castors Ø 125 mm: 2 fixed and 2 steering (one with brake)
- Front centralized safety lock
- Static load capacity: 1000 kg
- Built-in side bottle holder



	Art.
024006364	BW 2400S XL9/E-XXL-O
024006365	BW 2400S XL9/E-XXL-A
024006366	BW 2400S XL9/E-XXL-R

- n. 22 **42**: □
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm
- n. 12 **BW 141**: Ratcheting combination wrenches
8-9-10-11-12-13-14-15-16-17-18-19 mm
- n. 10 **BW 720L**: Impact sockets, long series, 1/2" □ □ □
10-12-13-15-17-19-21-24-27-30- mm
- n. 1 **BW 720/21**: Machine extension - 1/2" 125 mm
- n. 1 **BW 720/25**: Impact universal joint, 1/2" male and female square drives 64 mm
- n. 1 **BW 910/16F**: Adaptor - F3/8"xM1/2" E 3/8" - B 1/2"
- n. 1 **BW 920/16**: Adaptor - F1/2"xM3/4" E 1/2" - B 3/4"
- n. 20 **BW 920A**: Hexagon hand sockets, 1/2" □ □ □
8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm
- n. 8 **BW 920FTX**: Hand sockets for Torx® head screws, 1/2" □ □ □
E10-E12-E14-E16-E18-E20-E22-E24
- n. 8 **BW 920PE**: Socket drivers for hexagon screws, 1/2" □ □ □
5-6-7-8-9-10-12-14 mm
- n. 8 **BW 920PE-L**: Socket drivers for hexagon screws, long series, 1/2" □ □ □
5-6-7-8-9-10-12-14 mm
- n. 3 **BW 920PE-XL**: Socket drivers for hexagon screws, extra long series, 1/2" □ □ □ 10-12-14 mm
- n. 7 **BW 920TX**: Socket drivers for Torx® head screws, 1/2" □ □ □
T27-T30-T40-T45-T50-T55-T60
- n. 11 **BW 55**: Double open end wrenches □
6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22-21x23-24x27-30x32 mm
- n. 7 **BW 920TX-L**: Socket drivers for Torx® head screws, 1/2" □ □ □
T30-T40-T45-T50-T55-T60-T70
- n. 3 **BW 920TX-XL**: Socket drivers for Torx® head screws, extra long series, 1/2" □ □ □ T45-T50-T55
- n. 15 **BW 920AL**: Hexagon hand sockets, long series, 1/2" □ □ □
10-12-13-14-15-16-17-18-19-21-22-24-27-30-32 mm
- n. 1 **BW 920/21**: Extension bar - 1/2" 125 mm
- n. 1 **BW 920/22**: Extension bar - 1/2" 250 mm
- n. 1 **BW 920/25**: Universal joint, 1/2"
- n. 1 **BW 920/55**: Reversible ratchet □ □ 260 mm
- n. 8 **BW 97TX/SC8**: Set of 8 offset key wrenches, for Torx® head screws, burnished, with plastic support □ T9-T10-T15-T20-T25-T27-T30-T40
- n. 9 **BW 97TTX**: Offset key wrenches with handles for Torx® head screws □ T08-T09-T10-T15-T20-T25-T27-T30-T40
- n. 13 **BW 900**: Hexagon hand sockets, 1/4" □ □
□4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm



Scan the QR Code to access the web tab

Specs, media and documentation in one click.

