

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [67298-4090](#)
Status: **Active**
Overview: [Consumer USB Products](#)
Description: Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Dual Stacked, Type A, Gold (Au) Flash, White Housing, with 4 Beveled Metal Pins, Lead-Free

Documents:

[3D Model](#) [Test Summary TS-67298-008 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-67298-001 \(PDF\)](#)

General


| | |
|----------------|---------------------------------------|
| Product Family | I/O Connectors |
| Series | 67298 |
| Application | Wire-to-Board |
| Comments | 4 Beveled Metal Pins |
| Component Type | Receptacle |
| Overview | Consumer USB Products |
| Product Name | USB |
| Type | A |
| UPC | 822350050708 |

Physical

| | |
|--------------------------------|----------------|
| Boot Color | N/A |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Gender | Receptacle |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 5.667/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| PC Tail Length | 2.80mm |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Tray |
| Panel Mount | Yes |
| Pitch - Mating Interface | 2.00mm, 2.50mm |
| Pitch - Termination Interface | 2.00mm, 2.50mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Ports | 2 |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | 0°C to +50°C |
| Termination Interface: Style | Through Hole |
| Waterproof / Dustproof | No |

Electrical

| | |
|-------------------------------|-------------|
| Current - Maximum per Contact | 1.5A |
| Shield Type | Full Shield |
| Shielded | Yes |
| Voltage - Maximum | 30V DC |



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[67298Series](#)

Mates With

USB Type A Plug

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing
Test Summary

PS-67298-001
SD-67298-008
TS-67298-008

This document was generated on 12/18/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION