



RC safety socket outlet T55 Type A (PSE/SSF) 16 A 1+N-pole IFN 10 mA 125-230 V 2 MW in molded-plastic enclosure

Model	
product brand name	SETRON
product designation	SCHUKO socket outlet
cover version	complete enclosure
design of the special power supply unit	without special current supply
design of the socket according to VDE 0620 for severe conditions	No
design of the phase tap	No
General technical data	
marking of socket outlet	without imprint
mounting type	fixing with screw
surface processing	others
material	thermoplastic
tripping fault current rated value	10 000 mA
Supply voltage	
operating voltage rated value	230 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP54
Main circuit	
operational current rated value	16 A
Appearance	
color	miscellaneous
Product details	
product component	
• ejection equipment	No
• labeling field	No
• increased touch protection	No
• residual current device	Yes
• miniature fuse	No
• integrated functional lighting	No
• integrated light source	No
• integrated orientation lighting	No
• hinged lid	Yes
product feature	
• lockable	No
• halogen-free	Yes
• transparent	No
Product function	
product function	

- socket selectable
- overvoltage protection

Yes
No

Number

number of units	1
number of sockets switchable	0

Connections

arrangement of contacts diagonal	No
type of electrical connection	plug terminal

Mechanical Design

height	180 mm
width	119 mm
depth	95 mm
fastening method	surface mounting
net weight	698 g
material of the enclosure	plastic

Approvals Certificates

General Product Approval	other	Dangerous goods	Environment
--------------------------	-------	-----------------	-------------



[Confirmation](#)

[Transport Information](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SZ9206>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SZ9206>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SZ9206

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



