

Rear panel & door, PrismaSeT G, W 300mm, H 1450mm (27M), IP55, for extension duct

LVS08347

EAN Code: 3606481876706

Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Door Rear panel	
Device application	Low voltage electrical distribution	
Enclosure type	Functional enclosure delivered in kit form	
Provided equipment	1 x door for enclosure	
Additional information	Can be combined side by side and one on top of another	
type of front plate	Without	
Number of vertical modules [50 mm]	27	
Number of 18 mm modules per row	10	

Complementary

[Ui] rated insulation voltage	1000 V	
[In] rated current	630 A at 40 °C conforming to IEC 61439-2	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Surface finish	Smooth Matt	
Colour	White (RAL 9001)	
Width	300 mm	
Height	1450 mm	
Depth	260 mm	
Net weight	23 kg	
Quantity per set	Set of 1	

Environment

IP degree of protection	IP55 with door	
IK degree of protection	IK10 with door conforming to EN/IEC 62262	
Mechanical robustness Seismic tests - 2.5G conforming to IEC 60068-2-57		

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	11.000 cm
Package 1 Width	36.500 cm
Package 1 Length	144.000 cm
Package 1 Weight	24.500 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	15
Package 2 Height	68.000 cm
Package 2 Width	120.000 cm
Package 2 Length	200.000 cm
Package 2 Weight	390.000 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Environmental Disclosure

Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



- All dimensions are approximate and are in
 Also see technical documentation.