



Chemical protection

VITAL 175

Splashes | short wear



CHEMICAL PROTECTION
TYPE B

EN388



0010X

EN ISO 374-1



TYPE B
KPT

EN ISO 374-5



VIRUS

EN 421




CATEGORY 3



0334

DEXTERITY

EN420:
5/5



Dexterity and flexibility in light aggressive environments. Made from FSC® certified latex.

SPECIFIC ADVANTAGES



Comfort

- Excellent dexterity: a thin glove in a supple material



Guaranteed quality

- Chlorinated finish for better protection of products being handled
- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- FSC® certified latex
- Recycled packaging, Optimised individual packaging to limit plastic waste
- Recycled material in the packaging: 30 %

INDUSTRIES

- Mechanical industry
- Food industry
- Local Authorities (Cleaning)

APPLICATIONS

- Common cleaning Tasks
- Assembly of small, oil and grease free parts
- Handling household detergents








Chemical protection

VITAL 175

Splashes | short wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
0 0 1 0 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	K: Sodium hydroxide 40%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
TYPE B	
EN 421	RADIOACTIVE CONTAMINATION
	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria, fungi and virus
VIRUS	
	FOOD CONTACT
	French decree of 05/08/2020

PRODUCT DETAILS

Interior finish	Easy donning treatment
Exterior finish	Embossed texture, chlorinated
Material	FSC® certified latex
Cuff characteristic	Straight cuff
Colour.s	Yellow Beige
Length (cm)	31
Thickness (mm)	0.4
European sizes	6 7 8 9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/box 100 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/07/18/1373 Ext 01/07/18
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France