



149-164-4

1/4"-3/8"-1/2" Metric Tool Set, 164 Pcs



PRODUCT DETAILS

- Tool set - 164 pcs
- Made by high density polyethylene
- Metal latches provide an easy and resistant locking
- Handle for easy and comfortable transport
- Composition: Sockets, Ratchets, Pliers, Combination wrenches and Adaptors
- - 1/4" Socketry:
- - 1/4" Ratchet
- - Hexagonal Sockets: regular (4 to 12 mm), deep (4 to 12 mm)
- - Accessories
- - Bits: Torx (T10-T40)
- - TorxTammer (TR10-TR40)
- - 3/8" Socketry:
- - 3/8" Ratchet
- - Hexagonal Sockets: regular (8 to 19 mm), deep (8 to 19 mm)
- - Torx female Sockets (E8 to E20)
- - Accessories
- - Bits: Phillips (PH-1, PH-2), Pozidriv (PZ-1,PZ-2), Slotted (3 to 6 mm); TorxTammer (TR10-TR40)
- - Tools:
- - Combination wrenches 8 to 19
- - Ratcheting combination wrenches 12 to 14
- - Hex ball set
- - Pliers (Snipe nose and Combination pliers)
- - Screwdrivers (6 in 1 and stubby ratcheting screwdrivers)



PRODUCT ATTRIBUTES

Product					
149-164-4	100 mm	490 mm	370 mm	1415 g	100 x 370 x 490 mm



Socket 1/4" Deep Hex 8 mm
103-08-1



Socket 1/4" Deep Hex 9 mm
103-09-1



Socket 1/4" Deep Hex 10 mm
103-10-1



Socket 1/4" Deep Hex 11 mm
103-11-1



Socket 1/4" Deep Hex 12 mm
103-12-1



Extension 1/4" 50 mm
105-22-1



Extension 1/4" 100 mm
105-24-1



Universal Joint 1/4"
105-40-1



Bit Holder Square 1/4" with Hex 1/4"
105-48-1



Spinner Handle 1/4"
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth, 150 mm
105-70-1



Socket 3/8" Hex 8 mm
112-08-1



Socket 3/8" Hex 9 mm
112-09-1



Socket 3/8" Hex 10 mm
112-10-1



Socket 3/8" Hex 11 mm
112-11-1



Socket 3/8" Hex 12 mm
112-12-1



Socket 3/8" Hex 13 mm
112-13-1



Socket 3/8" Hex 14 mm
112-14-1



Socket 3/8" Hex 15 mm
112-15-1



Socket 3/8" Hex 16 mm
112-16-1



Socket 3/8" Hex 17 mm
112-17-1



Socket 3/8" Hex 18 mm
112-18-1



Socket 3/8" Hex 19 mm
112-19-1



Socket 3/8" Deep Hex 8 mm
113-08-1



Socket 3/8" Deep Hex 9 mm
113-09-1



Socket 3/8" Deep Hex 10 mm
113-10-1



Socket 3/8" Deep Hex 11 mm
113-11-1



Socket 3/8" Deep Hex 12 mm
113-12-1



Socket 3/8" Deep Hex 13 mm
113-13-1



Socket 3/8" Deep Hex 14 mm
113-14-1



Socket 3/8" Deep Hex 16 mm
113-16-1



Socket 3/8" Deep Hex 17 mm
113-17-1



Socket 3/8" Deep Hex 19 mm
113-19-1



Extension 3/8" 75 mm
115-20-1



Extension 3/8" 250 mm
115-24-1



Universal Joint 3/8"
115-40-1



3/8" to 1/2" Increasing Adaptor
115-44-1



3/8" to 1/4" Decreasing Adaptor
115-46-1



Bit Holder 3/8" to 5/16 Hex
115-48-1



Pear Type Ratchet 3/8", 72 Teeth,
200 mm
115-70-1



Socket 1/2" Deep Bihex 12 mm
124-12-1



Socket 1/2" Deep Bihex 13 mm
124-13-1



Socket 1/2" Deep Bihex 14 mm
124-14-1



Socket 1/2" Deep Bihex 15 mm
124-15-1



Socket 1/2" Deep Bihex 17 mm
124-17-1



Socket 1/2" Deep Bihex 18 mm
124-18-1



Socket 1/2" Deep Bihex 19 mm
124-19-1



Socket 1/2" Deep Bihex 21 mm
124-21-1



Socket 1/2" Deep Bihex 22 mm
124-22-1



Extension 1/2" 125 mm
125-23-1



Extension 1/2" 250 mm
125-25-1



Universal Joint 1/2"
125-40-1



Adaptor 1/2" to 3/8"
125-46-1



Ratchet 1/2" Pear Type, 72 Teeth,
250 mm
125-70-1



Ratcheting Combination Wrench 12
mm, Clip
18-12-1



Ratcheting Combination Wrench 13
mm, Clip
18-13-1



Ratcheting Combination Wrench 14
mm, Clip
18-14-1



Combination Wrench 8 mm, Clip
25-08-1



Combination Wrench 9 mm, Clip
25-09-1



Combination Wrench 10 mm, Clip
25-10-1



Combination Wrench 11 mm, Clip
25-11-1



Combination Wrench 12 mm, Clip
25-12-1



Combination Wrench 13 mm, Clip
25-13-1



Combination Wrench 14 mm, Clip
25-14-1



Combination Wrench 17 mm, Clip
25-17-1



Combination Wrench 18 mm, Clip
25-18-1



Combination Wrench 19 mm, Clip
25-19-1



1/4" Bit Torx Tamper TR10, 25 mm,
Box 5 Pcs
475-TR10-1



1/4" Bit Torx Tamper TR15, 25 mm,
Box 5 Pcs
475-TR15-1



1/4" Bit Torx Tamper TR20, 25 mm,
Box 5 Pcs
475-TR20-1



1/4" Bit Torx Tamper TR25, 25 mm,
Box 5 Pcs
475-TR25-1



1/4" Bit Torx Tamper TR27, 25 mm,
Box 5 Pcs
475-TR27-1



1/4" Bit Torx Tamper TR30, 25 mm,
Box 5 Pcs
475-TR30-1



1/4" Bit Torx Tamper TR40, 25 mm,
Box 5 Pcs
475-TR40-1



1/4" Bit T10, 25 mm, Box 10 Pcs
475-T10-1



1/4" Bit T15, 25 mm, Box 10 Pcs
475-T15-1



1/4" Bit T20, 25 mm, Box 10 Pcs
475-T20-1



1/4" Bit T25, 25 mm, Box 10 Pcs
475-T25-1



1/4" Bit T27, 25 mm, Box 10 Pcs
475-T27-1



1/4" Bit T30, 25 mm, Box 5 Pcs
475-T30-1



1/4" Bit T40, 25 mm, Box 5 Pcs
475-T40-1



Hex Ball Keys Holder 9 Pcs Set 1.5-10
mm
48-9-H



Combination Pliers 200 mm
Bimaterial Handles
601-200-1



Snipe Nose Pliers 160 mm Straight
Bimaterial Handles
612-160-1



Impact Socket 1/2" Hex 17 mm
167-17-1



Impact Socket 1/2" Hex 19 mm
167-19-1



Impact Socket 1/2" Hex 21 mm
167-21-1



Impact Socket 1/2" Hex 23 mm
167-23-1



Ratcheting Bit Holder Stubby 1/4" 6
Double Bits
475R-1/4-30



Screwdriver 6 in 1: Slotted, PH And
Nut Driver
475-5-1



Socket 1/2" Hex 14 mm
121-14-1



Socket 1/2" Hex 17 mm
121-17-1



Socket 1/2" Hex 18 mm
121-18-1



Socket 1/2" Hex 19 mm
121-19-1



Socket 1/2" Hex 20 mm
121-20-1



Socket 1/2" Hex 21 mm
121-21-1



Socket 1/2" Hex 22 mm
121-22-1



Socket 1/2" Hex 24 mm
121-24-1



Socket 1/2" Hex 27 mm
121-27-1



Socket 1/2" Hex 30 mm
121-30-1



Socket 1/2" Hex 32 mm
121-32-1