

1m Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXTMMHQ1M



The MXTMMHQ1M High Resolution VGA Cable (1-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

| | | |
|---------------------------------|---------------------------|---|
| Hardware | Warranty | Lifetime |
| | Cable Jacket Type | PVC - Polyvinyl Chloride |
| | Cable Shield Type | Aluminum-Mylar Foil with Braid |
| | Connector Plating | Nickel |
| | Fire Rating | CMG Rated (General Purpose) |
| | Number of Ferrites | 1 |
| | Regulatory Approvals | UL2919 |
| Performance | Impedance | 75 Ohm |
| Connector(s) | Connector A | 1 - VGA (15 pin, High Density D-Sub) Male |
| | Connector B | 1 - VGA (15 pin, High Density D-Sub) Male |
| Environmental | Humidity | 0 - 80 %RH |
| | Operating Temperature | 0 to 60 °C |
| | Storage Temperature | -20 to 80 °C |
| Physical Characteristics | Cable Length | 1 m [3.3 ft] |
| | Cable OD | 9 mm [0.4 in] |
| | Color | Black |
| | Max Connector Dimension | 34 mm [1.3 in] |
| | Product Length | 1 m [3.3 ft] |
| | Product Weight | 0.2 kg [0.4 lb] |
| | Wire Gauge | 28 AWG |
| Packaging Information | Package Quantity | 1 |
| | Shipping (Package) Weight | 0.2 kg [0.5 lb] |
| What's in the Box | Included in Package | 1 - 1 m Coax High Resolution Monitor VGA Cable - HD15 M/M 2 - Nuts |

Product appearance and specifications are subject to change without notice.