



Safety Data Sheet

RS Components Ltd

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 1 of 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

RS PRO Anti static wet/dry screen wipes,20/box

1.2. Relevant identified uses of the substance or mixture and uses advised against**Use of the substance/mixture**

PROC10 roller application or brushing ERC8A Extensive dispersive indoor use of processing aids in open systems
ERC8D Extensive dispersive outdoor application of processing aids in open systems

Uses advised against

Hand cleaning wipes

1.3. Details of the supplier of the safety data sheet**Manufacturer**

Company name: RS Components Ltd
Street: GB: Birchington Road
Place: GB-NN17 9RS GB-NN17 9RS Corby / Northants
Telephone: GB: +44 (0) 845 850 9900
E-mail: GB: RCustomerServicesUK@rs-components.com
Internet: GB: uk.rs-online.com
Responsible Department: GB: Tel: +44 (0) 1865 407333 (24hr)
+44 1235 239670 (24hr)

Supplier

Company name: RS Components Ltd
Glenview Industrial Estate
Street: Herberton Road
Place: IRL-NN17 9RS Rialto, Dublin 12
Telephone: Tel: +353 (0) 1 415 3100
E-mail: enquiries.ie@rs-components.com
Responsible Department: Tel: +44 (0) 1865 407333 (24hr)
+44 1235 239670 (24hr)

1.4. Emergency telephone number: IE: +353 (0)1 809 2166 (08:00 - 22:00)**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No 1272/2008**

This mixture is not classified as hazardous in accordance with Regulation (EC) No 1272/2008.

2.2. Label elements**Regulation (EC) No 1272/2008****Hazard statements**

EUH208 Contains benzisothiazilione. May produce an allergic reaction.
EUH210 Safety data sheet available on request.

Precautionary statements

P102 Keep out of reach of children.

Additional advice on labelling

The mixture is classified as not hazardous according to regulation (EC) No 1272/2008 [CLP].

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 2 of 8

Relevant ingredients

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	Classification (Regulation (EC) No 1272/2008)			
34590-94-8	Dipropylene glycol monomethyl ether			5-15%
	252-104-2			
2634-33-5	1,2-benzisothiazol-3(2H)-one; 1,2-benzisothiazolin-3-one			<0,1%
	220-120-9	613-088-00-6		
	Acute Tox. 2, Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, Skin Sens. 1A, Aquatic Acute 1, Aquatic Chronic 1; H330 H302 H315 H318 H317 H400 H410			

Full text of H and EUH statements: see section 16.

Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
		Specific Conc. Limits, M-factors and ATE	
2634-33-5	220-120-9	1,2-benzisothiazol-3(2H)-one; 1,2-benzisothiazolin-3-one	<0,1%
	inhalation: ATE 0,21 mg/l (dusts or mists); oral: ATE 450 mg/kg Skin Sens. 1A; H317: >= 0,036 - 100 Aquatic Acute 1; H400: M=1 Aquatic Chronic 1; H410: M=1		

Labelling for contents according to Regulation (EC) No 648/2004

preservation agents (Benzisothiazolinone).

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated clothing immediately and dispose off safely.

After inhalation

Provide fresh air.

After contact with skin

Wash with plenty of water. Frequently or prolonged contact with skin may cause dermal irritation. In case of skin irritation, seek medical treatment.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water. In case of troubles or persistent symptoms, consult an ophthalmologist.

After ingestion

Rinse mouth immediately and drink plenty of water.

Do NOT induce vomiting.

Seek medical advice immediately.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO2). Foam. Extinguishing powder.

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 3 of 8

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

In case of fire may be liberated: hydrocarbons. Carbon monoxide Carbon dioxide.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus. Move undamaged containers from immediate hazard area if it can be done safely.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures****General advice**

Provide adequate ventilation.

For non-emergency personnel

No data available

For emergency responders

No data available

6.2. Environmental precautions

Do not allow to enter into surface water or drains.

6.3. Methods and material for containment and cleaning up**For containment**

No data available

For cleaning up

No data available

Other information

Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents). Provide adequate ventilation.

6.4. Reference to other sections

No data available

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

Keep container tightly closed in a cool, well-ventilated place. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Protect against: heat.

Advice on general occupational hygiene

Wash hands before breaks and after work. Do not eat, drink or smoke when using this product. Provide fresh air. Keep out of the reach of children.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking. Protect from direct sunlight.

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 4 of 8

Further information on storage conditions

Keep in a cool, well-ventilated place.

7.3. Specific end use(s)

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
34590-94-8	(2-methoxymethylethoxy) propanol	50	308		TWA (8 h)	WEL

8.2. Exposure controls

Individual protection measures, such as personal protective equipment

Eye/face protection

Tightly sealed safety glasses.

Hand protection

Frequently or prolonged contact with skin may cause dermal irritation.

Wear suitable gloves.

Skin protection

Body protection: not required.

Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required.

Environmental exposure controls

Do not empty into drains.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	liquid
Colour:	transparent
Odour:	characteristic

Melting point/freezing point:	not determined
Flash point:	61 °C
Auto-ignition temperature:	not determined
pH-Value (at 20 °C):	7
Solubility in other solvents	
easily soluble	
Density (at 20 °C):	0,98-0,99 g/cm ³

Test method

DIN 51755

9.2. Other information

Information with regard to physical hazard classes

Explosive properties

No data available

Oxidizing properties

No data available

Other safety characteristics

Softening point:

DIN 51920

Further Information

No data available

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 5 of 8

SECTION 10: Stability and reactivity

10.1. Reactivity

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat.

10.5. Incompatible materials

Oxidizing agents, strong. Acid, concentrated.

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information

11.1. Information on hazard classes

Acute toxicity

Based on available data, the classification criteria are not met.

ATEmix calculated

ATE (oral) > 2000 mg/kg; ATE (dermal) > 2000 mg/kg; ATE (inhalation vapour) > 20 mg/l; ATE (inhalation dust/mist) > 5 mg/l

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
2634-33-5	1,2-benzisothiazol-3(2H)-one; 1,2-benzisothiazolin-3-one				
	oral	ATE 450 mg/kg			
	inhalation dust/mist	ATE 0,21 mg/l			

Irritation and corrosivity

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation: Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Contains benzisothiazolone. May produce an allergic reaction.

No information available.

Carcinogenic/mutagenic/toxic effects for reproduction

Germ cell mutagenicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Based on available data, the classification criteria are not met.

Reproductive toxicity: Based on available data, the classification criteria are not met.

No information available.

STOT-single exposure

Based on available data, the classification criteria are not met.

No information available.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

No information available.

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 6 of 8

Aspiration hazard

Based on available data, the classification criteria are not met.

No information available.

Information on likely routes of exposure

No information available.

Specific effects in experiment on an animal

No information available.

Additional information on tests

No information available.

Practical experience

No information available.

11.2. Information on other hazards**Endocrine disrupting properties**

No information available.

Other information

No information available.

SECTION 12: Ecological information**12.1. Toxicity**

Based on available data, the classification criteria are not met.

12.4. Mobility in soil

No adsorption in soil or sediment.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

No

12.7. Other adverse effects

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Disposal recommendations**

Dispose of waste according to applicable legislation.

List of Wastes Code - residues/unused products

200130 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents other than those mentioned in 20 01 29

List of Wastes Code - used product

200130 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents other than those mentioned in 20 01 29

List of Wastes Code - contaminated packaging

200130 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents other than those mentioned in 20 01 29

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 7 of 8

SECTION 14: Transport information**Land transport (ADR/RID)****14.2. UN proper shipping name:** Not restricted**Inland waterways transport (ADN)****14.2. UN proper shipping name:** Not restricted**Marine transport (IMDG)****14.2. UN proper shipping name:** Not restricted**Air transport (ICAO-TI/IATA-DGR)****14.2. UN proper shipping name:** Not restricted**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

No further relevant information available.

14.7. Maritime transport in bulk according to IMO instruments

No further relevant information available.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 75

National regulatory information

Water hazard class (D): 1 - slightly hazardous to water

SECTION 16: Other information**Abbreviations and acronyms**

Acute Tox. 2: Acute toxicity, hazard category 2

Acute Tox. 4: Acute toxicity, hazard category 4

Skin Irrit. 2: Skin irritation, hazard category 2

Eye Dam. 1: Serious eye damage, hazard category 1

Skin Sens. 1A: Skin sensitisation, hazard category 1A

Aquatic Acute 1: Hazardous to the aquatic environment, hazard category: Acute 1

Aquatic Chronic 1: Hazardous to the aquatic environment, long-term hazard category: Chronic 1

Relevant H and EUH statements (number and full text)

H302 Harmful if swallowed.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H318 Causes serious eye damage.

H330 Fatal if inhaled.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

EUH208 Contains benzisothiazilione. May produce an allergic reaction.

EUH210 Safety data sheet available on request.

Further Information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of



Safety Data Sheet

RS Components Ltd

RS PRO Anti static wet/dry screen wipes,20/box

Revision: 13.04.2026

Product code: 765-418

Page 8 of 8

processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the relevant ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)