

A-INL-PG13,5-P-GY - Counter nut



1411224

<https://www.phoenixcontact.com/gb/products/1411224>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg13.5, color: silver-gray RAL 7001



Commercial data

Item number	1411224
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 687 (C-2-2019)
GTIN	4046356923569
Weight per piece (including packing)	2.988 g
Weight per piece (excluding packing)	2.94 g
Customs tariff number	39269097
Country of origin	TR

A-INL-PG13,5-P-GY - Counter nut

1411224


<https://www.phoenixcontact.com/gb/products/1411224>

Technical data

Product properties

Product type	Flat nut
Thread type	Pg13.5

Dimensions

Dimensional drawing	
Length	6 mm
Diameter	20.4 mm
Connecting thread diameter	20.4 mm
Wrench size, counter nut	27 mm
Hexagon angular dimension	29 mm
Thread type connection side	Pg13.5

Material specifications

Material	PA
Flammability rating according to UL 94	V2

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-PG13,5-P-GY - Counter nut


1411224

<https://www.phoenixcontact.com/gb/products/1411224>



Drawings

Dimensional drawing



A-INL-PG13,5-P-GY - Counter nut



1411224

<https://www.phoenixcontact.com/gb/products/1411224>

Classifications

ECLASS

ECLASS-13.0	27140807
-------------	----------

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-PG13,5-P-GY - Counter nut



1411224

<https://www.phoenixcontact.com/gb/products/1411224>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk