



Cut protection

EXONIT 853

High risk - ISO D



GRIP & PROOF
TECHNOLOGY

CUT PROTECTION
LEVEL D



CATEGORY 2



DEXTERITY
EN ISO 21420:
5/5

Impact and cut (D) resistant glove offering superior dexterity and grip in oily environment (Made with grip&proof technology).

Reinforced with foam pads in the palm and nitrile crotch

SPECIFIC ADVANTAGES



Cut protection

- High cut protection for safety work

Impact protection

- TPR impact protective pads on back of hand and fingers



Durability

- Crotch reinforcement for enhanced durability. It offers better productivity and optimizes your costs.



Productivity

- Grip and Proof coating ensures an excellent grip in very oily environment . It also reduces muscle strain and boosts productivity



Skin protection

- Free of harmful substances: DMF Free



Additional benefits

- Optimised individual packaging format so as to limit plastic waste



Care for the environment

- Optimised individual packaging to limit plastic waste

INDUSTRIES

- Automotive/mechanical industry
- Mechanical industry
- Construction Industry (Masons / Plasterers)
- Construction Industry (Roofers/Tilers/Glazers)
- Petroleum industry
- Transport
- Manufacturing
- Industrial equipment / Metal transformation
- Mining / Utilities / Transportation
- Industrial maintenance

APPLICATIONS

- Handling bricks/blocks
- Installing steel structures
- Scaffold assembly
- Handling heavy parts with cut risk
- Maintenance with cut risk
- Handling oily mechanical parts
- Handling heavy metal sheets
- Machining of heavy parts
- Mechanical maintenance
- Handling of thick metal sheets



Cut protection

EXONIT 853

High risk - ISO D

LEGENDS

EN388		MECHANICAL HAZARDS	
		PERFORMANCE LEVELS (X = NOT TESTED)	
4	X	4	3 D P
0-4	0-5	0-4	0-4 A-F P
		Impact protection (optional)	
		Cut resistance according to ISO 13997	
		Puncture resistance	
		Tear resistance	
		Blade cut resistance	
		Abrasion resistance	

PRODUCT DETAILS

Interior finish	EVA foam pads in the palm, for better comfort
Gauge	13
Exterior finish	Non-slip grip
Material	Nitrile GRIP&PROOF coating
Cuff characteristic	Knitted Cuff
Colour.s	Black White Grey Yellow
European sizes	9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/box
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/12/23/2094
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE