

Rittal – The System.

Faster – better – everywhere.

Compact enclosures AE – AE 1260.500

Date : Dec 12, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Compact enclosures AE – AE 1260.500

created: 12.12.2019 build on www.rittal.com/uk-en



Product description

| | |
|--|--|
| Material: | Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal |
| Surface finish: | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated |
| Colour: | RAL 7035 |
| Protection category IP to IEC 60 529: | IP 66 |
| Protection category NEMA: | NEMA 4 |
| IK Code: | IK08 |
| Supply includes: | Enclosure with hinged door(s), of all-round solid construction Gland plate(s) in enclosure base Mounting plate Lock: 3 mm double-bit 3-point lock system |
| Basic material: | Sheet steel |

Product features

| | |
|----------------------------|---|
| Dimensions: | Width: 600 mm Height: 1200 mm Depth: 300 mm |
| Material thickness: | Enclosure: 1.5 mm Door: 2 mm |

Mounting plate: 3 mm

| | |
|--|--|
| Mounting plate: | Width: 540 mm Height: 1155 mm |
| Number of doors: | 1 |
| Door hinged on the right, may be swapped to the left: | yes |
| Lock version: | 3-point lock system |
| Number of locks: | 1 |
| Lock insert: | 3 mm double-bit |
| Gland plate, size: | 5 |
| Gland plate, qty.: | 1 |
| Packs of: | 1 pc(s). |
| Weight/pack: | 51 kg |
| EAN: | 4028177252448 |
| Customs tariff number: | 94032080 |
| ETIM 7.0: | EC000261 |
| ETIM 6.0: | EC000261 |
| eCl@ss 8.0/8.1: | 27180101 |
| eCl@ss 6.0/6.1: | 27180101 |
| Product description: | AE Compact enclosure, WHD: 600x1200x300 mm, Sheet steel, with mounting plate, single-door, 3-point lock system |

Approvals

| | |
|-------------------|--|
| Approvals: | Bureau Veritas CSA DNV-GL Lloyds Register of Shipping RRR Russian Maritime Register of Shipping TÜV UL + C-UL |
|-------------------|--|

| | |
|----------------------|---------------------------------------|
| Certificates: | EAC IK-Code Protection category |
|----------------------|---------------------------------------|

| | |
|----------------------|---------------------------|
| Declarations: | Declaration of conformity |
|----------------------|---------------------------|
