

FEATURES

- Both 290 mm and 550 mm height versions available
- 4 to 60 drawer versions suiting all your requirements
- Grey polypropylene (PP) cabinet
- Drawers
 manufactured from
 crystal clear
 polystyrene (PS)
- Galvanised steel shelves
- Temperature tolerance (-40 to +55°C)
- Self-adhesive labels supplied for each drawer
- Flexible and efficient storage

RS PRO 12 Drawer Storage Unit, PP, 138mm x Depth 175mm x Height 81mm, Grey

RS Stock No.: 909-6974



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO these plastic storage cabinets are ideal for all your everyday storage needs. They are built from a hard-wearing plastic, with galvanised steel shelves, making these units both durable and long lasting. They are ideal for storing all your small parts, as well as providing easy access

General Specifications

Drawers	12		
Drawer Material	crystal clear polystyrene		
Case Material	PP		
Colour	Grey		
Drawer size	138mm x Depth 175mm x Height 81mm		
Available Accessories to purchased separately	Cross Divider V-07 (5 Pcs/drawer), Length Divider V-078 (3 Pcs/drawer)		
Drawer Type	L-07		
Transparent Drawers	Yes		
Tilt Drawers	No		
Wall Mounted			
Applications	Garages, Workshops, Warehouses, Factories		

Mechanical Specifications

Overall Height	550mm
Overall Width	310mm
Overall Depth	180mm
Weight	4.6kg



Storage Drawer Dimensions

Storage Drawer Size (H x W x D)	Quantity Of Storage Drawer	Each Drawer Capacity
81mm x 138mm x 175mm	2 x 6	5kg
112mm x 600mm x 91mm	1 x 6	
164mm x 600mm x 133mm	1 x 5	
206mm x 600mm x 170mm	1 x 4	

Operation Environment Specifications

Cabinet Size Dra	Drawer	No of	Each Drawer	Each Drawer				
		Drawers in	External Size	Internal Size	RS Stock No			
HxWxD(mm) Ty	Туре	Cabinet	HxWxD(mm)	HxWxD(mm)				
	290mm HIGH CABINETS							
290 x 310 x 180	L-00	30	37 x 55 x 175	32 x 47 x 146	9096934			
290 x 310 x 180	L-01	24	37 x 69 x 175	32 x 61 x 146	9096943			
290 x 310 x 180	L-02	12	37 x 138 x 175	32 x 128 x 146	9096946			
290 x 310 x 180	L-04	12	59 x 92 x 175	55 x 82 x 146	9096940			
290 x 310 x 180	L-06	4	59 x 277 x 175	55 x 266 x 146	9096959			
290 x 310 x 180	L-07	6	81 x 138 x 175	74 x 128 x 146	9096952			
550mm HIGH CABINETS								
550 x 310 x 180	L-00	60	37 x 55 x 175	32 x 47 x 146	9096956			
550 x 310 x 180	L-01	48	37 x 69 x 175	32 x 61 x 146	9096965			
550 x 310 x 180	L-02	24	37 x 138 x 175	32 x 128 x 146	9096968			
550 x 310 x 180	L-04	24	59 x 92 x 175	55 x 82 x 146	9096962			
550 x 310 x 180	L-06	8	59 x 277 x 175	55 x 266 x 146	9096971			
550 x 310 x 180	L-07	12	81 x 138 x 175	74 x 128 x 146	9096974			