

Features

- Centre pivot screw and nut holds jaws together securely to avoid displacement when cutting.
- A one-piece forged steel handles with integral jaws.
- Jaw is precision machined, and induction hardened for added strength.
- Strong, long-lasting return leaf springs.
- Soft plastic grips for added comfort.

RS PRO Centre Conductor Cutting Nipper 3A

RS Stock No.: 0606317



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Centre Conductor Cutting Nipper 3A

A specialist tool for the telecoms industry. cuts centre conductor wires to the correct length. robust, durable, reliable.

Cut the prepared coaxial cable centre conductor wire to the correct stripping length for inner contact crimp termination.

For terminating type 43 connectors. Comfortable and easy to use.

Benefits

- Cut centre conductor wire to correct length – every time.
- Easier handling due to spring return.
- Designed for operator comfort.
- Built to last, with a robust construction and rust-resistant finish.

Applications

Used in the telecommunications industry to terminate type 43 connectors. Ideal for:

- Trimming the prepared centre conductor of coaxial cables 2000 and 3002 series to a length of between 3.2 mm and 3.3 mm as the stripping length required for inner contact crimp termination.

General Specifications

Type	Cutting Nipper
Materials Cut	Copper Wire
Non Sparking	No
Overall Length	110mm
Jaw Length	15mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	Steel with plastic grips
Maximum Cutting Capacity	0.61mm
Cut Type	Shear
Cutting Capacity	0.1mm – 0.61mm

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

