

LONG LIFE CUTTING HOLES IN VARIOUS MATERIALS

PRO

- 1 High-speed steel with 8% cobalt for durability and great performance
- 2 Bosch Power Change for removing plugs and changing hole saws efficiently



* vs Bosch HSS M3



BOSCH

PRO MULTI MATERIAL PC PLUS HOLE SAW SET

PRO


- ▶ For cutting holes in a variety of common construction and interior materials, eg wood, drywall, GFK and metals
- ▶ Highly efficient for electricians and plumbers: Long Life
- ▶ Lasts up to 2x longer than a standard HSS M3 Hole Saw
- ▶ For use with the Bosch Power Change Plus keyless arbor: offering accuracy and robustness



PRODUCT PROPERTIES		ORDERING INFORMATION				
Diameter mm	Working length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 6 949 509...	Part number
9-Pcs Electrician Set Multi Material PC Plus9-Pcs Electrician Set Multi Material PC Plus						
19	44	M0aP0k	9	1	240 675	2 608 594 423
25						
30						
35						
40						
40						
19	44	M0aP0k	9	1	240 682	2 608 594 424
25						
38						
44						
68						
68						
9-Pcs Plumber Set Multi Material PC Plus9-Pcs Plumber Set Multi Material PC Plus						
20	44	M0aP0k	9	1	240 712	2 608 594 427
25						
32						
38						
51						
51						
9-Pcs Electrician Set Multi Material PC Plus9-Pcs Electrician Set Multi Material PC Plus						
22	44	M0aP0k	9	1	240 729	2 608 594 428
29						
35						
44						
51						
51						
22	44	M0aP0k	9	1	240 736	2 608 594 429
29						
35						
44						
51						
51						
11-Pcs Electrician Set Multi Material PC Plus11-Pcs Electrician Set Multi Material PC Plus						
25	44	M0aP0k	11	1	240 743	2 608 594 430
32						
40						
54						
60						
68						


BOSCH

PRO MULTI MATERIAL PC PLUS HOLE SAW SET
PRO

PRODUCT PROPERTIES		ORDERING INFORMATION				
Diameter mm	Working length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 6 949 509...	Part number
76						
76						
14-Pcs Universal Set Multi Material PC Plus14-Pcs Universal Set Multi Material PC Plus						
20	44	M0aP0k	14	1	240 699	2 608 594 425
22						
25						
32						
35						
40						
44						
51						
60						
64						
64						
20	44	M0aP0k	14	1	240 705	2 608 594 426
22						
25						
32						
35						
40						
44						
51						
60						
68						
68						


BOSCH