


# CD COVER 40 - Cover profile

3240286

<https://www.phoenixcontact.com/gb/products/3240286>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, gray, width: 40 mm, length: 2000 mm

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240286             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BE7431              |
| Product key                          | BE7431              |
| Catalog page                         | Page 555 (C-5-2015) |
| GTIN                                 | 4046356470131       |
| Weight per piece (including packing) | 362 g               |
| Weight per piece (excluding packing) | 357.1 g             |
| Customs tariff number                | 39259020            |
| Country of origin                    | DE                  |

# CD COVER 40 - Cover profile

3240286

<https://www.phoenixcontact.com/gb/products/3240286>



## Technical data

### Product properties

|              |       |
|--------------|-------|
| Product type | Cover |
|--------------|-------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 40 mm   |
| Height | 2000 mm |
| Depth  | 11 mm   |
| Length | 2000 mm |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color                                  | stone gray (RAL 7030) |
| Material                               | PVC                   |
| Flammability rating according to UL 94 | V0                    |
| Components                             | Lead-free             |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 60 °C |
|---------------------------------|------------------|

# CD COVER 40 - Cover profile



3240286

<https://www.phoenixcontact.com/gb/products/3240286>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400776 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000727 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# CD COVER 40 - Cover profile

3240286

<https://www.phoenixcontact.com/gb/products/3240286>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)