

WATERPROOF RUGGED SOLAR POWERED CHARGER POWERMONKEY EXTREME

9000mAh



YOU CAN:
CHARGE 5V & 12V
DEVICES CAMERAS
IPADS IPHONES MOBILE
& SMARTPHONES GPS
E-READERS AND MORE



MPPT solar
technology

Digital LCD
screen

Standard USB
and 12V DC
port output

Shockproof and
waterproof
up to IP67

One touch
friction swipe
On/Off control



ADDITIONAL FEATURES

- 12V charging via in-car socket
- 3 way charging options (international mains charger, USB and solar panel)
- Low static wastage: 75% of charge retained after a year
- Advanced safety features

YOU CAN CHARGE VIA USB:

Device	Number of charges
iPad/tablet	50%-2 times
iPhone/smartphones	3-6 times

YOU CAN CHARGE VIA 12V:

Device	Number of charges
DVD Player	4 hours
Powertraveller cameranut/ Camera batteries cradle	2 times

Specifications

powermonkey extreme	
Total packaged weight	1.095kg
Dimensions (battery unit)	155 x 60 x 28mm
Dimensions (solar panel)	170 x 91 x 18mm (folded)
Battery type	HD Lithium Polymer
	Rechargeable
Battery capacity	9000mAh
Output voltage (USB port)	5v 700mAh
Output voltage (12V DC port)	800mAh
Input	5V 600mAh 2.5A
Energy	33.3WH
Charges	
Mobiles	•
iPods/MP3/MP4	•
iPads/Tablet computers	•
DVD players	•
Camera batteries	•
12V GPS	•
Special Features	
Water resistant	•
LCD screen	•
Solar panel	•
International Mains Charger	•
Includes MPPT technology	•
Colours	
Grey	•
Blue	•
Yellow	•
Red	•
Black	•

Contents

International Mains Charger	•
Connectors:	
- Nokia & Mini Nokia	•
- Samsung G600	•
- LG Chocolate	•
- Sony Ericsson	•
- Mini USB	•
- Micro USB	•
- Female USB	•
- DC4.0 connector	•
- DSI	•
- DC connector tip 'L53D'	•
DC Connection cable	•
USB charging cable	•
Zip case	•
User guide/instructions	•
Standard 1 year warranty	•
Female 12V in-car socket	•
Velcro strap	•

**POWERMONKEY
EXTREME
PROTECTIVE
WATERTIGHT
AQUASTRAP**

YOU CAN:
PROTECT YOUR POWERMONKEY
EXTREME FROM WATER WHILE
CHARGING YOUR DEVICES

available to buy from
www.powertraveller.com



powermonkey is a registered trademark of Powertraveller Limited registered in the UK and Europe.

"Made for iPod", "Made for iPhone", and "Made for iPad" mean that an electronic accessory has been designed to connect specifically to iPod, iPhone and iPad, respectively, and has been certified by the developer to meet Apple performance standards. Apple is not responsible for the operation of this device or its compliance with safety and regulatory standards. Please note that the use of this accessory with iPod, iPhone or iPad may affect wireless performance.

iPad, iPhone and iPod are trademarks of Apple Inc., registered in the U.S. and other countries.



For customer support, email us at
support@powertraveller.com

POWERTRAVELLER LIMITED

Ceratech House, Omega Park, Wilsom Road,
Alton, Hampshire GU34 2QE UK
t +44 (0) 1420 542980
info@powertraveller.com
www.powertraveller.com

powertraveller
without boundaries™

9000mAh

YOU CAN:
CHARGE 5V &
12V DEVICES
CAMERAS IPADS
IPHONES MOBILE
& SMARTPHONES
GPS E-READERS
AND MORE

WATERPROOF RUGGED SOLAR POWERED CHARGER POWERMONKEY EXTREME

Originally launched in 2011 after five years in development, the powermonkey extreme is the culmination of feedback from real power users in some of the most remote locations on the planet and completely embodies Powertraveller's understanding of customer's power requirements when they are "off-grid". Since its launch, the powermonkey extreme has undergone some serious upgrades to further cement the product's reputation as "charger of choice" in the outdoor and adventure travel market.

The powermonkey extreme houses a massive 9000mAh capacity Lithium Polymer battery and offers users real power in a compact, durable shell. The unit is capable of recharging most 5V devices including iPhones/smartphones up to 4 times, a Garmin Edge 800 up to 6 times, standard mobiles up to 8 times and iPad up to 2 times depending on model. As well as a 5V USB socket, the extreme features a 12V DC output port that is capable of charging SLR camera batteries, portable DVD players and much more directly from the unit.

The powermonkey extreme can be recharged in three ways; via the universal mains charger, via the solar panel or via USB. The rugged, clam-shell design solar panel offers 3 Watt max output, allowing full recharge of the powermonkey extreme within 18-22 hours in optimum light conditions. The powermonkey extreme also has a solar energy detection feature which activates the incorporated state-of-the-art MPPT (maximum power point tracker) technology, allowing the solar panel to charge the powermonkey unit more efficiently in low light conditions. Users can also simultaneously use the solar panel to charge the powermonkey extreme whilst it is charging their device. The solar panel can be attached to tents or rucksacks via the included Velcro strap, so is perfect for hiking and is designed to take the knocks and spills of both the power hungry adventurer and the busy traveller.

The powermonkey extreme is waterproof for 30 minutes up to 1 metre and shock resistant - perfect for the outdoor, marine and adventure enthusiast, as well as military and aid agencies. When used in conjunction with the aquastrap, the powermonkey extreme will be kept watertight whilst it charges your devices.



powertraveller
without boundaries™