



GREEN LITE

EN ISO 21420 : 2020



EN 388



4 1 3 1 A

EN 407



X 1 X X X X



EN 388 : 2016 +A1 : 2018

• ABRASION	: 4/4
• BLADE CUT	: 1/5
• TEARING	: 3/4
• PERFORATION	: 1/4
• CUTTING BY SHARP OBJECT (ISO 13997)	: A/F

EN 407 : 2020

• FIRE BEHAVIOR	: X/4
• CONTACT HEAT	: 1/4
• CONVECTIVE HEAT	: X/4
• RADIANT HEAT	: X/4
• SMALL SPLASHES OF LIQUID METAL	: X/4
• LARGE SPLASHES OF LIQUID METAL	: X/4

FEATURES

- SEAMLESS TRICOTTE GLOVE, LINING RECYCLED POLYETHYLENE TEREPHTHALATE (PET) 45%, NYLON 40%, ELASTHANNE 10%, SPANDEX 5%, GAUGE 15
- NITRILE MICRO FOAM COVERING PALM
- COLOR GRAY/BLACK

RECOMMENDED USES

- DIY WORK
- ASSEMBLING CARS, HANDLING SMALL PARTS
- LOGISTICS AND WAREHOUSING, ROAD AND RAILROAD WORK
- AIRPORT SECURITY AND BAGGAGE HANDLING

CE MARKING

- THIS MARKING SIGNIFIES COMPLIANCE WITH THE ESSENTIAL REQUIREMENTS PROVIDED FOR BY EUROPEAN REGULATION 2016/425, RELATING TO PERSONAL PROTECTIVE EQUIPMENT

SAFETY, COMFORT, AND DEXTERITY

- DEXTERITY: LEVEL 5
- THIS GLOVE DOES NOT CONTAIN ANY SUBSTANCES AT LEVELS WHICH ARE KNOWN OR SUSPECTED TO HAVE ADVERSE EFFECTS ON THE HYGIENE OR HEALTH OF THE USER UNDER THE EXPECTED CONDITIONS OF USE

PACKAGING

- IN CASE OF DECONDITIONING, A COPY OF THE NOTICE MUST BE ENCLOSED WITH THE SMALLEST PACKAGING
- BAG OF 10 PAIRS
- BOX OF 100 PAIRS

LIMITATIONS OF PROTECTION

- DO NOT USE FOR HANDLING OBJECTS AT TEMPERATURES ABOVE 100°C
- DO NOT USE FOR HANDLING CHEMICALS OR LIQUIDS

PRECAUTIONS FOR USE

- WEAR GLOVES ON DRY, CLEAN HANDS
- IT IS RECOMMENDED TO CARRY OUT A PRELIMINARY TEST UNDER REAL CONDITIONS OF USE, WHICH MAY DIFFER FROM EU TYPE TESTING
- BEFORE RE-USE, CHECK GLOVES FOR DEFECTS, HOLES, TEARS, ABNORMAL WEAR, ETC

STORAGE AND MAINTENANCE

- STORE PRODUCTS IN A DRY, COOL, WELL-VENTILATED PLACE, AWAY FROM LIGHT, SUNLIGHT AND ULTRAVIOLET RAYS, LEAVING THEM IN THEIR ORIGINAL PACKAGING
- WHEN CORRECTLY STORED, GLOVES RETAIN THEIR PROPERTIES WITHOUT UNDERGOING MAJOR CHANGES
- NO SPECIAL MAINTENANCE IS RECOMMENDED
- WASHING INSTRUCTIONS UNDER ISO 6330: 3 DOMESTIC WASHING CYCLES 60°MAX

DISPOSAL

- END-OF-LIFE DESTRUCTION MUST BE CONTROLLED AND COMPLY WITH EUROPEAN TRACEABILITY AND ENVIRONMENTAL REQUIREMENTS

AVAILABLE SIZES

6 7 8 9 10 11 12



EU TYPE CERTIFICATE ISSUED IN ACCORDANCE WITH MODULE B REGULATION (EU) 2016/425 - SATRA N°2777

THE EU DECLARATION OF CONFORMITY IS AVAILABLE ON REQUEST. CONTACT US VIA OUR WEBSITE WWW.GUYARD-SA.COM, "CONTACT" SECTION