




Part Number : [5051470290](#)
Product Description : 2.00mm Pitch Easy-On Flexi-Latch FPC-to-Board Connector, Right-Angle, Surface Mount, Positive Inertia Lock, 2 Circuits
Series Number : 505147
Status : Active
Product Category : FFC / FPC Connectors



Documents & Resources

Drawings
[5051470290_sd.pdf](#)

3D Models and Design Files
[5051470290_stp.zip](#)

Specifications
[5051479200-200.pdf](#)
[5051470000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
 - IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	505147
Description	2.00mm Pitch Easy-On Flexi-Latch FPC-to-Board Connector, Right-Angle, Surface Mount, Positive Inertia Lock, 2 Circuits
Product Name	Easy-On
UPC	887191676289

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Physical

Actuator Type	Flexi-Latch
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Contact Position	Bottom
Durability (mating cycles max)	25
Flammability	94V-0
Mated Height	4.85mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold

Material - Resin	Liquid Crystal Polymer
Net Weight	418.100/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Wire/Cable Type	FPC only

Use with Part(s)

Description	Part Number
2.00mm Pitch Easy-On Flexi-Latch FPC-to-Board Plug Jacket, 2 Circuits	<u>5051480208</u>
