



59S/54C-1

**1/4" Bit Set for
Slotted/Phillips/Pozidriv/Hex/
TORX®/TORX®
Tamper/Robertson Screws - 54
Pcs**



PRODUCT DETAILS

- For Phillips, Pozidriv, Hexagonal, TORX®, TORX® tamper, Robertson and Slotted head screws
- Includes 54 pieces: 53 Standard bits + 1 magnetic bit holder
- TORX® bits have colored sleeve to easy identify the size of the tip
- For universal use
- High performance alloy steel
- Zinc phosphate finish
- 1/4" hex drive DIN 3126 and ISO 1173, style C 6.3
- Reduced-shank 50mm bits provides enhanced accessibility
- 75 mm Hex universal magnetic bit holder with retaining ring (style E 6.3)
- Resistant glass fiber reinforced case, tough and durable for good protection of the content
- The patented case has a 180° locking function: case stays in open position even if turned [up to 500g of added weight] without closing on your fingers
- The lid and body of the case can be split for flexible organizing in trolley drawer or toolkit.
- The box is designed to be stacked on top of each other without sliding off, when using multiple sets
- Swiveling racks allow space optimization and easy access to the bits
- Sticker delivered within the set for personalization and user identification
- Delivered in a cardboard sleeve



Follow the Fish!



PRODUCT ATTRIBUTES

Product			
59S/54C-1	54	45 x 105 x 175 mm	556 g

SET CONTENT



**1/4" Standard Screwdriver Bit for
Slotted Head Screws 0.8 mm x 5.5
mm x 25 mm - 3 Pcs/Blister Pack**
59S/0.8-5.5-3P



**1/4" Standard Screwdriver Bit for
Robertson # 1 Head Screws 25 mm
- 3 Pcs/Blister Pack**
59S/R1-3P



**1/4" Standard Screwdriver Bit for
Robertson # 2 Head Screws 25 mm
- 3 Pcs/Blister Pack**
59S/R2-3P



**1/4" Hex Universal Magnetic Bit
Holder with Retaining Ring 75 mm -
5 Pcs/Plastic Box**
KMR753



**1/4" Standard Screwdriver Bit for
Pozidriv PZ2 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50PZ2-5P



**1/4" Standard Screwdriver Bit for
Pozidriv PZ3 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50PZ3-5P



**1/4" Standard Screwdriver Bit for
Phillips PH3 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50PH3-5P



**1/4" Standard Screwdriver Bit for 4
mm Hex Screws 25 mm - 5
Pcs/Plastic Box**
59S/H4-5P



**1/4" Standard Screwdriver Bit for
Philips PH1 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PH1-10P



**1/4" Standard Screwdriver Bit for
Pozidriv PZ2 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PZ2-10P



**1/4" Standard Screwdriver Bit for
Phillips PH2 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50PH2-5P



**1/4" Standard Screwdriver Bit for
Pozidriv PZ1 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50PZ1-5P

Follow the Fish!





**1/4" Standard Screwdriver Bit for
TORX® T20 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50T20-5P



**1/4" Standard Screwdriver Bit for
TORX® T30 Head Screw 25 mm - 5
Pcs/Plastic Box**
59S/T30-10P



**1/4" Standard Screwdriver Bit for
TORX® T15 Head Screw 25 mm -
10 Pcs/Plastic Box**
59S/T15-10P



**1/4" Standard Screwdriver Bit for
TORX® T20 Head Screw 25 mm -
10 Pcs/Plastic Box**
59S/T20-10P



**1/4" Standard Screwdriver Bit for
TORX® T30 Head Screws 50 mm -
5 Pcs/Plastic Box**
59S/50T30-5P



**1/4" Standard Screwdriver Bit for
Philips PH2 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PH2-10P



**1/4" Standard Screwdriver Bit for 2
mm Hex Screws 25 mm - 5
Pcs/Plastic Box**
59S/H2-5P



**1/4" Standard Screwdriver Bit for
2.5 mm Hex Screws 25 mm - 5
Pcs/Plastic Box**
59S/H2.5-5P



**1/4" Standard Screwdriver Bit for 5
mm Hex Screws 25 mm - 5
Pcs/Plastic Box**
59S/H5-5P



**1/4" Standard Screwdriver Bit for 6
mm Hex Screws 25 mm - 5
Pcs/Plastic Box**
59S/H6-5P



**1/4" Standard Screwdriver Bit for
Philips PH3 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PH3-10P



**1/4" Standard Screwdriver Bit for
Pozidriv PZ1 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PZ1-10P



**1/4" Standard Screwdriver Bit for
Pozidriv PZ3 Head Screws 25 mm -
10 Pcs/Plastic Box**
59S/PZ3-10P



**1/4" Standard Screwdriver Bit for
TORX® T10 Head Screw 25 mm -
10 Pcs/Plastic Box**
59S/T10-10P



**1/4" Standard Screwdriver Bit for
TORX® T25 Head Screw 25 mm -
10 Pcs/Plastic Box**
59S/T25-10P



**1/4" Standard Screwdriver Bit for
TORX® T40 Head Screw 25 mm - 5
Pcs/Plastic Box**
59S/T40-10P

Follow the Fish!





**1/4" Standard Screwdriver Bit for
TORX® TR10 Tamper-Resistant
Screws 25 mm - 5 Pcs/Plastic Box
59S/TR10-5P**



**1/4" Standard Screwdriver Bit for
TORX® TR20 Tamper-Resistant
Screws 25 mm - 5 Pcs/Plastic Box
59S/TR20-5P**



**1/4" Standard Screwdriver Bit for
TORX® TR25 Tamper-Resistant
Screws 25 mm - 5 Pcs/Plastic Box
59S/TR25-5P**



**1/4" Standard Screwdriver Bit for
TORX® TR30 Tamper-Resistant
Screws 25 mm - 5 Pcs/Plastic Box
59S/TR30-5P**



**1/4" Standard Screwdriver Bit for
Phillips PH1 Head Screws 50 mm -
5 Pcs/Plastic Box
59S/50PH1-5P**



**1/4" Standard Screwdriver Bit for
TORX® T15 Head Screws 50 mm -
5 Pcs/Plastic Box
59S/50T15-5P**



**1/4" Standard Screwdriver Bit for
TORX® T25 Head Screws 50 mm -
5 Pcs/Plastic Box
59S/50T25-5P**



**1/4" Standard Screwdriver Bit for
TORX® T40 Head Screws 50 mm -
5 Pcs/Plastic Box
59S/50T40-5P**



**1/4" Standard Screwdriver Bit for
TORX® T10 Head Screws 50 mm -
5 Pcs/Plastic Box
59S/50T10-5P**

Follow the Fish!



Contact: info@bahco.com / www.bahco.com