


# Datasheet

Recessed Pan Machine Screws  
 Stainless Steel A2-304  
 DIN 7985



d1	M1.6	M2	M2.5	M3	M3.5	M4	M5	M6	M8
d2	3.20	4.00	5.00	6.00	7.00	8.00	10.00	12.00	16.00
k	1.42	1.72	2.12	2.52	2.82	3.25	3.95	4.75	6.15
Recess no.	0	1	1	1	2	2	2	3	4

Please view our full range listing below

RS Stock No	Size (mm)	RS Stock No	Size (mm)	RS Stock No	Size (mm)	RS Stock No	Size (mm)	RS Stock No	Size (mm)
1795681	M1.6 × 2	1795691	M2.5 × 4	9141490	M3 × 25	7976200	M4 × 40	528902	M6 × 12
1795682	M1.6 × 3	9141472	M2.5 × 5	9141494	M3 × 30			528918	M6 × 16
1795683	M1.6 × 4	528716	M2.5 × 6			9141510	M5 × 6	528924	M6 × 20
1795684	M1.6 × 5	9141481	M2.5 × 8	9141504	M3.5 × 6	7976204	M5 × 8	528930	M6 × 25
1795685	M1.6 × 6	7976190	M2.5 × 10	9141507	M3.5 × 8	7976213	M5 × 10	9141532	M6 × 30
1795686	M1.6 × 8	528722	M2.5 × 12	528788	M3.5 × 12	528867	M5 × 12	9141535	M6 × 35
1795647	M1.6 × 10	9141484	M2.5 × 16	528794	M3.5 × 20	528873	M5 × 16	9141539	M6 × 40
		9141488	M2.5 × 20			528889	M5 × 20	9141548	M6 × 50
1795688	M2 × 3	1795692	M2.5 × 25	528801	M4 × 6	528895	M5 × 25	9141541	M6 × 60
9141462	M2 × 4			7976197	M4 × 8	7976216	M5 × 30		
9141466	M2 × 5	9141497	M3 × 5	528817	M4 × 10	7976210	M5 × 35	9141545	M8 × 12
528693	M2 × 6	528738	M3 × 6	528823	M4 × 12	9141513	M5 × 40	9141554	M8 × 16
9141475	M2 × 8	7976193	M3 × 8	528839	M4 × 16	9141517	M5 × 45	9141557	M8 × 20
9141478	M2 × 10	528744	M3 × 10	528845	M4 × 20	9141526	M5 × 50	9141551	M8 × 25
528700	M2 × 12	528750	M3 × 12	528851	M4 × 25				
1795689	M2 × 16	528766	M3 × 16	7976207	M4 × 30	9141529	M6 × 8		
1795690	M2 × 20	528772	M3 × 20	9141501	M4 × 35	9141523	M6 × 10		