

## Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Full Metal Construction
- Available in different sizes

## RS PRO ESD Vertical Upright

RS Stock No.: 0687823

0687824

0687825

0687624

0687625

0687626

0687668


0687669

0687670

0687693

0687694

0687695



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The extension frame is a key component that significantly enhances the functionality of workstations by enabling the attachment of additional equipment. It provides support for a variety of accessories, allowing for more efficient organization of the workspace and better utilization of ESD tables.

Made from 2.0 mm thick sheet metal, the frame ensures high durability and resistance to damage, even under heavy use. Equipped with mounting cutouts spaced 50 mm apart, it allows for flexible installation of perforated panels and other accessories.

With the option to add a central post, the frame can be adapted to handle larger loads and specific requirements. Designed to span the entire width of the table, the extension frame integrates seamlessly with existing equipment, offering full support and optimization of the workspace. It is an indispensable addition to modern workstations where precise organization and maximum functionality are essential.

Accessories compatible with L & H Type workbenches

## Accessory Type: ESD Vertical Upright (Frame)

| Stock No. | Product Name                                   | Compatible RS PRO ESD workbench (mm) |
|-----------|------------------------------------------------|--------------------------------------|
| 0687823   | ESD high vertical upright (frame), 1180x1800   | 1200                                 |
| 0687824   | ESD medium vertical upright (frame), 1180x1500 | 1200                                 |
| 0687825   | ESD low vertical upright (frame), 1180x1100    | 1200                                 |
| 0687624   | ESD high vertical upright (frame), 1480x1800   | 1500                                 |
| 0687625   | ESD medium vertical upright (frame), 1480x1500 | 1500                                 |
| 0687626   | ESD low vertical upright (frame), 1480x1100    | 1500                                 |
| 0687668   | ESD high vertical upright (frame), 1780x1800   | 1800                                 |
| 0687669   | ESD medium vertical upright (frame), 1780x1500 | 1800                                 |
| 0687670   | ESD low vertical upright (frame), 1780x1100    | 1800                                 |
| 0687693   | ESD high vertical upright (frame), 1980x1800   | 2000                                 |
| 0687694   | ESD medium vertical upright (frame), 1980x1500 | 2000                                 |
| 0687695   | ESD low vertical upright (frame), 1980x1100    | 2000                                 |