





Product no.: 676EW

Side cutter, same as 676E, with optional safety device "wire catcher"



This is the narrowest head shape.

The underside is relieved and facilitates optimum access even to extremely hard-to-reach areas.

source images

## The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 600 Micro is a range of miniature precision cutters that offers a wide variety of head shapes for access in difficult to reach areas. These micro cutters are suitable for SMD and leads (670EP, 670EPF). The cutters are made from high grade tool steel with cutting edges hardened to 63-65HRc. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

	Туре	Туре	of Cut	Cutti	ing	Ca	pac	ity														
Series 600	Micro &	2600		n 0,030,1 h .0001 .003		,	,	,	<b>0,6</b> .023	0,7 .027	,	,	<b>1,0</b> .039	,	<b>1,2</b> .047	<b>1,3</b> .051	<b>1,4</b> .055	,	,	1,7 .066	<b>1,8</b> .070	
6	612N 2612N		Semi Flush																			
	622N 2622N		Flush																			
	622TX		Flush / Carbide																			
	632N 2632N		Super Full Flush					-								-						
6	622NA		Flush																			
G	622NB 2622NB		Flush					+														٦
	676E		Flush								-											
	776E		Super Full Flush					-			-											٦
	632NCF		Super Full Flush	only fo	or sof	t mat	erials:	silic	one,	rubbe	er											
ol	670E		Flush																			
- AL	670EP		Flush																			
	670EPF		Flush	for mic	cro pi	itches	s unde	r 0,5	mm													









PRECISION TOOLS



Wel	ler®
	Erem

Technical Data							
Technical Data							
Length mm	110						
Length of cutting edges mm	9						
Head width mm	9						
Head thickness mm	6						
Head length mm	16						
Max. cutting capability – hard wire mm							
Weight in oz	1.764						
Length of cutting edges Inches	0.354						
Head width Inches	0.354						
Head thickness Inches	0.236						
Head length Inches	0.630						
ESD-safe	on						
Cut	Flush						
Max. cutting capability – medium hardness mm	Ø 0,6						
Max. cutting capability – copper wire mm	Ø 0,8						
Length inches	4.331						
Weight in g	50						

Weller Tools GmbH Carl-Benz-Straße 2 74354 Besigheim Germany Phone: +49 (0) 7143 / 580-0 Fax.: +49 (0) 7143 / 580-108 Email: info@weller-tools.com Web: www.weller-tools.com