

PTFIX-NS35 LQ - DIN rail adapter

1092937

<https://www.phoenixcontact.com/gb/products/1092937>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 for accommodating 2.5 mm², 4 mm², and 10 mm² FIX blocks in vertical direction, color: gray, packing unit: 200



Commercial data

Item number	1092937
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BEAZ11
Product key	BEAZ11
GTIN	4055626909257
Weight per piece (including packing)	4.5 g
Weight per piece (excluding packing)	4.5 g
Customs tariff number	39269097
Country of origin	PL

PTFIX-NS35 LQ - DIN rail adapter

1092937

<https://www.phoenixcontact.com/gb/products/1092937>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	28.6 mm
Height	58.1 mm
Depth	11 mm
Depth on NS 35/7,5	15 mm
Depth on NS 35/15	22.5 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

PTFIX-NS35 LQ - DIN rail adapter

1092937

<https://www.phoenixcontact.com/gb/products/1092937>



Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1092937>

DNV				
Approval ID: TAE00002TT-05				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	500 V	24 A	-	-

BV				
Approval ID: 59146/A0 BV				

PTFIX-NS35 LQ - DIN rail adapter



1092937

<https://www.phoenixcontact.com/gb/products/1092937>

Classifications

ECLASS

ECLASS-13.0	27370419
-------------	----------

ETIM

ETIM 9.0	EC001024
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX-NS35 LQ - DIN rail adapter



1092937

<https://www.phoenixcontact.com/gb/products/1092937>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk