

Chem FR

Chem FR Boilersuit with Hood, Velcro Adjustment Wrists and Ankles and Reflective Tape.

Chem FR is specifically developed to offer additional protection from heat, flame and electrostatic hazards.

Cotton is included in the fabrics backing material providing additional comfort to wearers, while a PVC coating provides optimum chemical protection.

Features

- ▲ Protection against chemicals, heat, flame and electrostatic hazards
- ▲ Double storm facing with velcro closure for increased protection
- ▲ Ring-pull zip for easy donning and doffing when wearing gloves
- ▲ Helmet-compatible hood with elasticated drawcord adjustment
- ▲ Elasticated back waist for improved fit
- ▲ Velcro wrists fastening for easy adjustment
- ▲ Reinforced knee patches for durability and protection
- ▲ Adjustable velcro ankles for improved fit
- ▲ Reflective tapes enhances visibility
- ▲ Base fabric includes cotton for additional comfort
- ▲ Garment can be machine washed
- ▲ Garment can be reused if not contaminated or damaged
- ▲ Stitched and high frequency welded seams

Colours available

-  Green*
-  HV Orange
-  Navy*
-  S/Yellow*

*Minimum order quantities apply



Certification

					
EN 14605:2005 +A1:2009	EN 14605:2005 +A1:2009 Type 3	EN 14605:2005 +A1:2009 Type 4	EN ISO 11612:2015 A1, B1, C1	EN 1149-5:2018 t ₅₀ < 4 secs	EN 343:2019 3 1



SUITABLE INDUSTRIES & APPLICATIONS

-  Chemical
-  Waste
-  Transport
-  Oil & Gas
-  Water treatment

- ▲ Chemical Cleaning
- ▲ Chemical Road Freight
- ▲ Chemical Site Handling
- ▲ Heavy Industry
- ▲ Oil and Gas
- ▲ Petrochem Refining
- ▲ Shipping
- ▲ Tank Cleaning

Chem FR

Chem FR Boilersuit with Hood, Velcro Adjustment Wrists and Ankles and Reflective Tape.

Product Options

Item	Code	Colour	Hood	Elasticated Wrists	Elasticated Ankles	Reflected Tape
BOILERSUIT	FRBH	Green	✓	–	–	–
BOILERSUIT	FRBH-EW	Green or S/Yellow	✓	✓	–	–
BOILERSUIT	FRBH-R	Green	✓	–	–	–
BOILERSUIT	FRBH-EW-R	Green or HVO	✓	✓	–	✓
BOILERSUIT	FRBH-EIWA	Green	✓	✓	✓	–
BOILERSUIT	FRBH-EDW-EA-R	Green	✓	✓	✓	✓
BOILERSUIT	FR 10123	Green or HVO	✓	✓	✓	✓



Sizing - (Wearer's Measurements)

Size	Body Height (cm)	Chest (cm)	Waist (cm)	Inside Leg (cm)
S	166-170	90-98	81-89	73
M	170-174	98-106	89-97	75
L	174-179	106-114	97-104	78
XL	179-184	114-122	104-112	81
2XL	179-184	122-130	112-120	81
3XL	179-184	130-138	120-128	81
4XL	179-184	138-146	128-136	81

Storage and Maintenance

We recommend storing Chem FR garments in their original packaging, away from UV sources. After use, please follow the care instructions provided on the label. To remove any contamination, the ChemFR can be machine washed at 40°C and allow it to drip dry in a shaded area, away from UV sources. It is advisable to store Chem FR clothing in a cool, dry, and clean environment.

NOTE: For hygiene purposes, it is recommended that the garment be worn by the same individual.

Chemical Resistance Data

For chemical permeation data, please contact our sales department at sales@globusgroup.com.

Compliance Statement - EU (CE)

Product conforms to the requirement of Regulation (EU) 2016/425 of the European Parliament and of the Council as Personal Protective Equipment (PPE).

Type-Examination, (Module B), Certificates issued by:

EU – CCQS Certification Services Limited Block 1, Blanchardstown Corporate Park, Ballycoolin Rd, Blanchardstown, Dublin 15, D15 AKK1 Ireland [N.B. No. **2384**].

PPE is subject to the conformity assessment procedure, conformity to type based on Quality Assurances of the production process, (Module D), under the surveillance of the Notified Body:

EU – SGS Fimko Oy, Takomotie 8, FI-00380, Helsinki, Finland [N.B. No. **0598**].

Economic Operator [EU]: Globus EMEA Ltd., 51 Dawson Street, Dublin, D02 AN25, Ireland.