

DELTA switch device insert FM, Control switch switchover 10A 250V



| Model                                       |                            |
|---|----------------------------|
| Product brand name                          | DELTA                      |
| Type of installation switch / rotary switch | No                         |
| Type of light source                        | Control switch             |
| Type of composition                         | basic element              |
| Design of the operating mechanism           | rocker/button              |
| General technical data                      |                            |
| Type of switch                              | toggle switch              |
| Mounting type                               | fixing with claw and screw |
| Surface processing                          | others                     |
| Material                                    | others                     |
| Supply voltage                              |                            |
| Operating voltage / Rated value             | 250 V                      |
| Protection class                            |                            |
| Protection class IP                         | IP20                       |
| Switching capacity                          |                            |
| Switching capacity current                  | 10 A                       |

| Current                                   |                  |
|---|------------------|
| Switching current / for fluorescent lamps | 0 A              |
| Main circuit                              |                  |
| Operating current / rated value           | 10 A             |
| Appearance                                |                  |
| Appearance                                | not applicable   |
| Color                                     | miscellaneous    |
| Product details                           |                  |
| Product component                         |                  |
| • Labeling field                          | No               |
| • Signaling contact                       | No               |
| • Pushbutton switch                       | No               |
| Product feature / halogen-free            | Yes              |
| Number                                    |                  |
| Number of actuating rockers               | 1                |
| Connections                               |                  |
| Type of electrical connection             | Plug-in terminal |
| Mechanical Design                         |                  |
| Height                                    | 70 mm            |
| Mounting type                             | flush mounted    |
| Material / of the enclosure               | metal            |
| Certificates                              |                  |
| Reference code                            |                  |
| • acc. to DIN EN 61346-2                  | S                |
| • acc. to DIN EN 81346-2                  | SF               |

| General Product Approval | Declaration of Conformity | Test Certificates |
|--------------------------|---------------------------|-------------------|
|--------------------------|---------------------------|-------------------|



ÖVE



VDE



EG-Konf.

[Miscellaneous](#)

[Type Test Certificates/Test Report](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TA2108>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5TA2108>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5TA2108](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TA2108)

