

22MM PLASTIC ROUND COMPLETE UNIT
COMBINATION: SELECTOR SWITCH LATCHING 2
SWITCH POSITIONS O-I NON-ILLUMINATED SCREW
TERMINAL,
1NO+1NC WITH HOLDER BLACK

Actuator:

Design of the operating mechanism

handle

Front ring:

Product component / front ring

Yes

Material / of the front ring

plastic

Color / of the front ring

black

Enclosure:

Shape / of the housing front

round

material / of the housing

plastic

General technical details:

Number of control points

1

Type of voltage

• of the operating voltage

AC/DC

Operating voltage / rated value

• minimum

V

5

• maximum

V

400

Design of the electrical connection

screw-type terminals

Number of switching positions

2

Product extension / optional / fluorescent materials

No

Resistance against shock

• for devices without incandescent lamp / according to IEC 60068-2-27

<= 50g

Resistance against vibration / according to IEC 60068-2-6

20 ... 200 Hz: 5g

Operating cycles / maximum

1/h

1,000

Mechanical operating cycles as operating time / typical

300,000

Item designation

• according to DIN EN 61346-2

S

• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750

S

Auxiliary circuit:

Number of NC contacts / for auxiliary contacts		1
Number of NO contacts / for auxiliary contacts		1
Number of change-over switches / for auxiliary contacts		0

Installation/mounting/dimensions:

Type of mounting		front mounting
Shape / of the installation hole		round
Installation width	mm	28.5
Mounting diameter	mm	22
Mounting height	mm	24
Tightening torque / of the screws in the bracket / maximum	N·m	1

Ambient conditions:

Ambient temperature		
• during operating	°C	-25 ... 70
• during storage	°C	-40 ... 80
Protection class IP		IP66

Certificates/approvals:

General Product Approval



CQC



CSA

[ROSTEST](#)



UL

Test Certificates

[Manufacturer](#)

Shipping Approval



ABS



BUREAU
VERITAS



DNV



LRS



PRS



RINA

other

[Manufacturer](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator



<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3201-2HA11/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3201-2HA11



last change:

Oct 31, 2011