

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 42-474

Flexible full-length heat barrier.

Previously known as: Crusader Flex 42474



Heat



Heavy Duty

## Superior heat resistance with complete protection for hand and wrist.

- Designed for intermittent handling of dry hot objects up to 250°C / 480°F
- Provides resistance to cuts and abrasion
- Enhances grip on dry and oily surfaces
- Comfortable & flexible: sweat absorbent nonwoven felt inner liner



### Industries

- Automotive
- Chemical
- Food Processing

### Applications

- Press injection molding
- Handling molded structural parts
- Testing
- Welding


Previously known as: Crusader Flex 42474

### Key Features

- Non-woven felt insulation and a full-length heat barrier designed for intermittent handling of dry objects up to 250°C / 480°F
- Two-piece construction eliminates outseams for better finger comfort, dexterity and flexibility
- Bonded nitrile coating protects against snags, punctures, abrasions and cuts
- Provides excellent grip when handling dry or oily surfaces
- Comfortable & flexible: sweat absorbent non-woven felt inner
- Contains no asbestos
- Compliant to FDA food handling requirements

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm <sup>®</sup> 42-474	<b>Liner Material:</b> Non-Woven Polyester, Polycotton <b>Cuff Style:</b> Gauntlet	N/A	9, 10	343-356 mm; 13.5-14 inches	• 12 Pair Per Bag; 6 Bags Per Carton

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.