

G Shape with Inline PTT and Lapel Mic

› 11ECH1040



Features

- › Soft, discreet and comfortable
- › Environmental PU cable reinforced with Kevlar
- › Discreet communication in sensitive environments
- › Suitable for many applications including; security personnel, hotel and catering staff, etc

Technical Specification

Speaker

Dimensions:	$\Phi 15.0\text{mm} * 6.0\text{mm}$
Impedance:	$320 \pm 14\% @ 1000\text{Hz}$
Rated Input Power	100mW
Rated Output Power	300mW
Sound Pressure Level:	$105 \pm 3\text{db} @ 1000\text{Hz}$

Microphone

Type:	Electric Microphone
Impedance:	2.2 kOhm
Sensitivity:	$-40 \pm 3\text{db} @ 1000\text{Hz}$ (0db = 1V/PA)
Operating Voltage:	1.1-10VDC

PTT

Dimensions:	34.9 * 14.2 * 11.8mm
-------------	----------------------

> Connectors

	Product Code	Description
	11ECH1040 M1	G Shape with Inline PTT and Lapel Mic with Motorola Two-pin right angle . Suitable for Motorola: GP300, CP040, XTN446, HYT: TC600.TC610/TC620,TC446
	11ECH1040 M1A	G Shape with Inline PTT and Lapel Mic with Motorola Two-pin right angle . Suitable for Motorola: XTNi and XTNiD
	11ECH1040 M4	G Shape with Inline PTT and Lapel Mic with Motorola multiple pin M4 . Suitable for Motorola: GP328, GP340, GP360, GP380
	11ECH1040 M5	G Shape with Inline PTT and Lapel Mic with Motorola multiple pin M5 . Suitable for Motorola: GP344, HYT: TC-780, TC3000; Kirisun: PT7200
	11ECH1040 M7	G Shape with Inline PTT and Lapel Mic with MOTOTRBO multiple pin . Suitable for Motorola DP3400 / DP3600
	11ECH1040 K1	G Shape with Inline PTT and Lapel Mic with Kenwood two-pin . Suitable for Kenwood: TK-2100, 2102, 2130, 2160, TK-3100, 3160, TK-3101, TK-3102, TK-3130
	11ECH1040 K2	G Shape with Inline PTT and Lapel Mic with Kenwood Multiple pin . Suitable for Kenwood: TK-280, TK-290, TK-380, TK-385, TK-390, TK-480, TK-481, TK-2041, TK-2140, TK-3140, TK-3148
	11ECH1040 Y2	G Shape with Inline PTT and Lapel Mic with Yaesu/ Vertex Standard One-Pin Right Angle with screw . Suitable for Vertex: VX-10, VX-110, VX-160, VX-180, VX-210, VX-210A, VX-200, VX-300, VX-400, VX-410, VX-420, VX-150, VX-2R
	11ECH1040 Y6	G Shape with Inline PTT and Lapel Mic with Yaesu/ Vertex Standard Multiple-Pin . Suitable for Vertex: VX-820, VX-821, VX-824, VX-829, VX-920, VX-921, VX-924, VX-929
	11ECH1040 T1	G Shape with Inline PTT and Lapel Mic - Tait Suitable for Tait: TP8110, TP8115, TP8120, TP8135, TP8140, TP7110