

20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Fiber Media Converter



The ETCHS2U 20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Media Converters lets you add an un-managed, 20-slot media converter chassis to your rack or cabinet to provide central power and cooling.

The media converter rack includes a single 200W power supply to centrally power all 20 slots, with an additional slot to add a redundant power supply (ETCHS2UPSU) for maximum up-time. It also includes two cooling fans (one per side) to help extend the life of your media converters.

A perfect accessory to the StarTech.com ET series 2 converters, the 2U chassis is designed so that all critical components (Power, Fans and Media Converter Cards) are hot swappable to avoid network disruption.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

o Centrally mount and power up to 20 media converter units with a single chassis, while providing additional cooling and optional redundant power

The StarTech.com Advantage

- converters into one space, while providing central power and cooling, for a streamlined rackmount solution
- o Chassis consolidates your media o Modular design lets you hotswap your media converter cards, fans, or add an additional power supply without downtime

Certifications













Technical Specifications

WARRANTY INFORMATION

HARDWARE

Fan(s)
Yes

Fans
2 - 80 mm

Frame Type
Open Frame
Mounting Options
Front Mount (Front Only)

2U

PERFORMANCE

U Height

 Air Flow Rate
 59.37 CFM

 MTBF
 65,000 Hours (25°C)

 Noise Level
 44.5 dBA

POWER

Input Current 2.2 A

Input Voltage 110V-240V AC

Output Current 16.6 A

Output Voltage 12V DC

Power Consumption (In Watts)

Power Source Standard 120V Power Cords

ENVIRONMENTAL

Humidity 5–90% RH Non-condensing

Operating Temperature 0°C to 60°C (32°F to 140°F)

Storage Temperature -10°C to 70°C (14°F to 158°F)

PHYSICAL CHARACTERISTICS

Color	Black
Material	Steel
Product Height	16.4 cm [6.5 in]
Product Length	39.4 cm [15.5 in]
Product Width	51.7 cm [20.4 in]
Rail Thickness	1 mm [0 in]
Weight of Product	6.1 kg [13.4 lb]

PACKAGING INFORMATION

Package Height	19.1 cm [7.5 in]
Package Length	56.7 cm [22.3 in]
Package Width	43.8 cm [17.2 in]
Shipping (Package) Weight 8.4 kg [18.5 lb]	

WHAT'S IN THE BOX

Included in Package	1 - 2U Media Converter Chassis
	3 - Power Cords (NA/EU/UK)
	1 - Grounding Screw
	1 - Instruction Manual