
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKO06MPN
COUPLING HALF: Coupler
BODY MATERIAL: Brass
FUNCTION: Double Shut-Off
CONNECTION SIZE: 4x6 MM
CONNECTION TYPE: Tube

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

APPLICATION	Industrial Machinery
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	10.0
WEIGHT	0.011 kg
INTERCHANGE TYPE	European Profile
CONNECTION SIZE	4x6 mm
BRAND	Parker
MINIMUM OPERATING TEMPERATURE	-20 °C
DIAMETER	2.7 mm (nominal)
MINIMUM OPERATING TEMPERATURE	-4 °F
FLOW RATE	1.2 L/min (water)
MAXIMUM OPERATING PRESSURE	507 psi
LENGTH	34 mm
PRODUCT SERIES	Series 20
MAXIMUM OPERATING PRESSURE	35 bar
INDUSTRY	General Industrial
TECHNOLOGY	Pneumatics
MAXIMUM OPERATING TEMPERATURE	100 °C
INDUSTRY	Healthcare & Life Sciences

FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
MAXIMUM OPERATING TEMPERATURE	212 °F
BRAND	Rectus
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
FLOW RATE	130 L/min (air)
REGION OF ORIGIN	Germany
CONNECTION TYPE	Tube With hose nut, without spring guard
APPLICATION	Pharma
COUPLING HALF	Coupler
PLATING TYPE	Nickel-Plated
APPLICATION	Food & Beverages
BODY MATERIAL	Brass
TECHNOLOGY	Fluid & Gas Handling
PRODUCT TYPE	Pneumatic Quick Couplings
VALVE TYPE	Standard Valve
OPERATION TYPE	Sleeve
FUNCTION	Double Shut-Off
HEX SIZE	9 mm (external)
PRODUCT STYLE	Quick Connect
VALVE INCLUDED	Yes
APPLICATION	Medical
SEAL MATERIAL	NBR
SLEEVE MATERIAL	Brass
COMPATIBLE FITTING	Series 20 Plug
DIVISION	Low Pressure Connectors Europe Division