

Series 7400 ESD Kraftform torque screwdrivers with a customised factory pre-set measurement value, with quick-release chuck, 7456 ESD x 0.3-1.0 Nm
 Series 7400 Kraftform Torque Screwdrivers, adjustable to customer requirements within the specified measurement range



EAN:	4013288188298	Size:	170x40x40 mm
Part number:	05074828010	Weight:	134 g
Article number:	7400 ESD customized pre-set, Halfmoon	Country of origin:	CZ
		Customs tariff number:	82054000

- Customized pre-set, adjustable Kraftform ESD torque screwdriver
- ESD-safe tool thanks to surface resistance of $\leq 10^9$ Ohm
- Kraftform handle for fast and ergonomic screwdriving
- Suitable for bits with 4 mm halfmoon and 4 mm HIOS drive
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached

Wera torque screwdriver. Safe protection against electrostatic charge and associated damage. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required. The torque can be changed within the measuring range with the extra tool 05137003001. Afterwards you can check the set value using an off-the-shelf torque tester. Rapidaptor quick-release technology for rapid bit changes. Unlimited loosening torque for slackening stuck screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with a 4 mm Halfmoon drive (Wera series 9) and a 4 mm HIOS drive (Wera series 21).
 Please note: 1 Ncm = 0.01 Nm.



Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_adjustable_to_customer_requirements_within_the_specified_measurement_range_7400_05074828010-4013288188298

Wera - 7400 ESD customized pre-set, Halfmoon
 05074828010 - 4013288188298

Wera Werkzeuge GmbH
 Korzerter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Series 7400 ESD Kraftform torque screwdrivers with a customised factory pre-set measurement value, with quick-release chuck, 7456 ESD x 0.3-1.0 Nm
 Series 7400 Kraftform Torque Screwdrivers, adjustable to customer requirements within the specified measurement range



Individual pre-setting



Wera torque screwdriver. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required.

Wera ESD Tools




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

For Halfmoon and HIOS Bits



Features a combination bitholder for both bits with Halfmoon and bits with HIOS drive.

Kraftform



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_adjustable_to_customer_requirements_within_the_specified_measurement_range_7400

Wera - 7400 ESD customized pre-set, Halfmoon
 05074828010 - 4013288188298

Wera Werkzeuge GmbH
 Korztert Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Series 7400 ESD Kraftform torque screwdrivers with a customised factory pre-set measurement value, with quick-release chuck, 7456 ESD x 0.3-1.0 Nm
Series 7400 Kraftform Torque Screwdrivers, adjustable to customer requirements within the specified measurement range



Further versions in this product family:

art. no.	Nm	mm	mm	inch
05074826010	7455 ESD	0.1-0.34	89	138
05074828010	7456 ESD	0.3-1.0	89	138

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_adjustable_to_customer_requirements_within_the_specified_measurement_range_7400_05074828010.html

Wera - 7400 ESD customized pre-set, Halfmoon
05074828010 - 4013288188298

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de