

Features

- 3 frame types, open, cross braced and solid clad all available in 3 duties.
- Shelves and storage accessories are a common fitting to all frames styles.
- Accessories feature clip-in fitting so that any changes are quickly and easily made.
- Wide range of sizes and load capacities
- Specially designed “T” profile uprights and welded box section beams maximise the strength of the system.
- UK manufactured to ISO certified quality and environmental standards.

RS PRO Euro Shelving Systems



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Euro Shelving Systems

Euro shelving system is a truly versatile and interchangeable system ideal for office or departmental storage, storerooms, stockrooms, maintenance stores and industry in general.

Euro shelving with light grey powder coated finish contains ActiveCoat antimicrobial technology which minimises the risk of bacterial cross-contamination.



General Specifications

Product Name	Euro Shelving Systems
Upright Colour	<input type="radio"/> Light Grey
Shelf Colour	<input type="radio"/> Light Grey
Dimensions	See details below

Stock No.	Brand	Product Name	Dimension (H x W x D mm)
xxx-xxxx 214187	RS PRO	Euro Open Starter (SHELVING KIT)	2100 x 1000 x 300
xxx-xxxx 214188	RS PRO	Euro Open Starter (6 shelves starter bay)	2100 x 1000 x 400
xxx-xxxx 214077	RS PRO	Euro Open Starter (6 shelves starter bay)	2100 x 1000 x 450
xxx-xxxx 214078	RS PRO	Euro Open Starter (SHELVING KIT EXT)	2100 x 1000 x 300
xxx-xxxx 214080	RS PRO	Euro Open Starter (6 shelves ext. bay)	2100 x 1000 x 400
xxx-xxxx 214081	RS PRO	Euro Open Starter (6 shelves ext. bay)	2100 x 1000 x 450
xxx-xxxx 214083	RS PRO	Euro Side closed & Rear Open Stater (SHELVING KIT)	2100 x 1000 x 300
xxx-xxxx 214084	RS PRO	Euro Side closed & Rear Open Stater (SHELVING KIT)	2100 x 1000 x 400
xxx-xxxx 214086	RS PRO	Euro Side closed & Rear Open Stater (SHELVING KIT)	2100 x 1000 x 450
xxx-xxxx 214087	RS PRO	Euro Side closed & Rear Open Stater (SHELVING KIT EXT)	2100 x 1000 x 300
xxx-xxxx 214089	RS PRO	Euro Side closed & Rear Open Stater (SELVING KIT)	2100 x 1000 x 400
xxx-xxxx 214090	RS PRO	Euro Side closed & Rear Open Stater (SHELVING KIT)	2100 x 1000 x 450
xxx-xxxx 214092	RS PRO	Euro Closed / Clad Starter (SHELVING KIT)	2100 x 1000 x 300
xxx-xxxx 214093	RS PRO	Euro Closed / Clad Starter (6 shelves starter bay)	2100 x 1000 x 400
xxx-xxxx 214095	RS PRO	Euro Closed / Clad Starter (6 shelves starter bay)	2100 x 1000 x 450
xxx-xxxx 214096	RS PRO	Euro Closed / Clad Starter (SHELVING KIT)	2100 x 1000 x 300
xxx-xxxx 214097	RS PRO	Euro Closed / Clad Starter (6 shelves ext. bay)	2100 x 1000 x 400
xxx-xxxx 214099	RS PRO	Euro Closed / Clad Starter (6 shelves ext. bay)	2100 x 1000 x 450

Euro Open Starter



Euro Open Starter - Ext



Euro Closed/Clad Starter



Euro Closed/Clad Starter - Ext





Upright caps locate in top of uprights to provide capping for safety and improved appearance

Cross brace provides rear bracing & stability for open back shelving bays.

Choice of 3 upright duties to meet various loads and applications




Simply slot the clip into the uprights to create an extremely rigid structure yet allowing for quick and easy re-positioning of shelves.



For safety, shelf support clips are designed to prevent accidental shelf dislodgement whilst being extremely easy to use.



Shelves utilise box section construction at the front and rear for load bearing strength and rigidity.



Rear cladding, closes off the rear of the shelf level, stopping items from falling out of the back of bays.

Clad frames stop products stored on adjacent bays from getting mixed together

Foot plates spread loads of the upright, protecting the floor surface and allowing shelving to be fixed to the floor for stability, when required